

AVA5P-50FX-42



AVA5P-50FX-42, HELIAX® Andrew Virtual Air™ Coaxial Cable, corrugated copper, 7/8 in, black PE jacket

Alternative products available:

AVA5-50FX	AVA5-50FX, HELIAX® Andrew Virtual Air™ Coaxial Cable, corrugated copper, 7/8 in, black PE jacket (Halogen free jacketing non-fire-retardant)
-----------	--

Product Classification

Product Type	Coaxial wireless cable
Product Brand	HELIAX®
Product Series	AVA5-50FX
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa Not available in the United States or Canada

General Specifications

Flexibility	Standard
Jacket Color	Black
Performance Note	Attenuation values typical, guaranteed within 5%

Dimensions

Diameter Over Dielectric	24.13 mm 0.95 in
Diameter Over Jacket	27.991 mm 1.102 in
Inner Conductor OD	9.449 mm 0.372 in
Outer Conductor OD	25.4 mm 1 in
Nominal Size	7/8 in

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm
------------------------	---------------

AVA5P-50FX-42

Capacitance	73 pF/m 22.25 pF/ft
dc Resistance, Inner Conductor	2.888 ohms/km 0.88 ohms/kft
dc Resistance, Outer Conductor	1.313 ohms/km 0.4 ohms/kft
dc Test Voltage	6000 V
Inductance	0.184 μ H/m 0.056 μ H/ft
Insulation Resistance	100000 MOhms-km
Jacket Spark Test Voltage (rms)	8000 V
Operating Frequency Band	1 – 5000 MHz
Peak Power	91 kW
Velocity	90 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
800–960 MHz	1.101	26.36
1700–2200 MHz	1.101	26.36

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.113	0.034	74.43
1.5	0.138	0.042	60.73
2.0	0.16	0.049	52.56
10.0	0.359	0.11	23.37
20.0	0.51	0.156	16.46
30.0	0.627	0.191	13.39
50.0	0.814	0.248	10.32
85.0	1.068	0.326	7.86
88.0	1.088	0.332	7.72
100.0	1.162	0.354	7.23
108.0	1.209	0.368	6.95
150.0	1.433	0.437	5.86
174.0	1.548	0.472	5.43
200.0	1.665	0.507	5.05
204.0	1.682	0.513	4.99
300.0	2.059	0.628	4.08
400.0	2.398	0.731	3.5

AVA5P-50FX-42

450.0	2.553	0.778	3.29
460.0	2.583	0.787	3.25
500.0	2.7	0.823	3.11
512.0	2.735	0.834	3.07
600.0	2.977	0.907	2.82
700.0	3.235	0.986	2.6
800.0	3.478	1.06	2.42
824.0	3.534	1.077	2.38
894.0	3.694	1.126	2.27
960.0	3.841	1.171	2.19
1000.0	3.927	1.197	2.14
1218.0	4.377	1.334	1.92
1250.0	4.44	1.353	1.89
1500.0	4.912	1.497	1.71
1700.0	5.268	1.605	1.59
1794.0	5.429	1.655	1.55
1800.0	5.439	1.658	1.54
2000.0	5.771	1.759	1.46
2100.0	5.933	1.808	1.42
2200.0	6.091	1.856	1.38
2300.0	6.247	1.904	1.34
2500.0	6.55	1.996	1.28
2700.0	6.845	2.086	1.23
3000.0	7.272	2.217	1.15
3400.0	7.819	2.383	1.07
3600.0	8.083	2.464	1.04
3700.0	8.213	2.503	1.02
3800.0	8.342	2.542	1.01
3900.0	8.47	2.581	0.99
4000.0	8.596	2.62	0.98
4100.0	8.722	2.658	0.96
4200.0	8.846	2.696	0.95
4300.0	8.969	2.734	0.94
4400.0	9.092	2.771	0.92
4500.0	9.213	2.808	0.91

AVA5P-50FX-42

4600.0	9.333	2.845	0.9
4700.0	9.453	2.881	0.89
4800.0	9.572	2.917	0.88
4900.0	9.689	2.953	0.87
5000.0	9.806	2.989	0.86

Material Specifications

Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Copper
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	254 mm 10 in
Minimum Bend Radius, single Bend	127 mm 5 in
Number of Bends, minimum	15
Number of Bends, typical	30
Tensile Strength	159 kg 350.535 lb
Bending Moment	27.1 N-m 239.855 in lb
Flat Plate Crush Strength	1.3 kg/mm 72.797 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +70 °C (-67 °F to +158 °F)
Storage Temperature	-70 °C to +70 °C (-94 °F to +158 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C

Packaging and Weights

Cable weight	0.46 kg/m 0.309 lb/ft
---------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

AVA5P-50FX-42

CENELEC

EN 50575 compliant, Declaration of Performance (DoP) available

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

