

# 2-1716219-3 | C-004-L2-5L-M04BK/40G/GY/FS/B

---

Fire Survival (120min) Fiber Optic Cable, multimode, OM3, 4-fiber, loose tube, gel filled, ULSZH, 2000 m. Provides Rodent Resistance.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-L2

## General Specifications

<b>Armor Type</b>	Corrugated steel
<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB SYSTEM F.O. CABLE X-1716219-3 INT/EXT FIRE SURVIVAL 4x50/125 OM3 [Serial number] [metre mark]
<b>Fibers per Subunit, quantity</b>	4
<b>Total Fiber Count</b>	4

## Dimensions

<b>Diameter Over Jacket</b>	12.7 mm   0.5 in
-----------------------------	------------------

## Optical Specifications

<b>Fiber Type</b>	OM3, bend insensitive
-------------------	-----------------------

## Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	TIA-492AAAD (OM4)
-----------------------------	-------------------

## Environmental Specifications

<b>EN50575 CPR Cable EuroClass Fire Performance</b>	B2ca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1b

<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)
<b>Flame Test Listing</b>	EN 50399   IEC 60332-1-2
<b>Flame Test Method</b>	EN 50399   IEC 60331-25 (120) Fire resistance: 120 minutes at 750 °C (no fiber break)   IEC 60332-1-2   IEC 60754-2   IEC 61034-2

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

