

HELIAX® Hybrid Cable, UL Type TC-OF-ER

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable, copper and fiber
Product Brand	HELIAX®

General Specifications

Application	Remote radio head
Cable Type	Wireless feeder
Conductors, quantity	4
Construction Type	Shielded
Fiber Short Description	RFF – 12AWG
Fiber Type, quantity	6
Fibers per Subunit, quantity	6
Inner Shield (Tape) Material	Corrugated aluminum
Jacket Color	Black
Outer Shield (Tape) Material	PVC
Strength Members	Glass reinforced plastic rod
Subunit, quantity	1
Total Fiber Count	6
Water Blocking Method	Water blocking tape(s) Water blocking threads

Dimensions

Buffer Tube/Subunit Diameter	3.048 mm 0.12 in
-------------------------------------	--------------------

760187260 | HTC-6SM-412-APV

Diameter Over Jacket 14.732 mm | 0.58 in


Conductor Gauge 12 AWG

Electrical Specifications

dc Resistance Note Maximum value based on a standard condition of 20 °C (68 °F)

dc Resistance, maximum 5.413 ohms/km | 1.65 ohms/kft

Representative Image



Material Specifications

Ripcord Material Para-aramid synthetic fiber

Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded 292.1 mm | 11.5 in

Minimum Bend Radius, multiple bends, unloaded 147.32 mm | 5.8 in

Minimum Bend Radius, single bend, unloaded 101.6 mm | 4 in

Tensile Load, long term, maximum 266.893 N | 60 lbf

Tensile Load, short term, maximum 889.644 N | 200 lbf

Compression 2.25 kg/mm | 126 lb/in

Compression Test Method FOTP-41

Flex 25 cycles

Flex Test Method FOTP-104

Impact 2.17 ft lb | 2.942 N-m

Impact Test Method FOTP-25

Twist 10 cycles

Twist Test Method FOTP-85

760187260 | HTC-6SM-412-APV

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20 | Telcordia GR-409

Environmental Space Wireless installation

Packaging and Weights

Cable weight 305.074 kg/km | 205 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

CS-8G-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable