

# 760217505 | HEC-24SM-610M-AHF

---

HELIAX® Hybrid Cable

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable, copper and fiber
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Application</b>	Remote radio head
<b>Cable Type</b>	Wireless feeder
<b>Conductors, quantity</b>	6
<b>Construction Type</b>	Shielded
<b>Fiber Short Description</b>	RFF-10 mm <sup>2</sup>
<b>Fiber Type, quantity</b>	24
<b>Fibers per Subunit, quantity</b>	12
<b>Inner Shield (Tape) Material</b>	Corrugated aluminum
<b>Jacket Color</b>	Black
<b>Outer Shield (Tape) Material</b>	Fire retardant PE
<b>Strength Members</b>	Glass reinforced plastic rod
<b>Subunit, quantity</b>	2
<b>Total Fiber Count</b>	24
<b>Water Blocking Method</b>	Water blocking tape(s)   Water blocking threads


## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	5.334 mm   0.21 in
<b>Diameter Over Jacket</b>	26.416 mm   1.04 in
<b>Conductor Gauge</b>	10 mm <sup>2</sup> class 2

## Electrical Specifications

<b>dc Resistance Note</b>	Maximum value based on a standard condition of 20 °C (68 °F)
<b>dc Resistance, maximum</b>	1.831 ohms/km   0.558 ohms/kft

## Representative Image



## Material Specifications

**Ripcord Material** Para-aramid synthetic fiber

## Mechanical Specifications

<b>Minimum Bend Radius, multiple bends, loaded</b>	530.86 mm   20.9 in
<b>Minimum Bend Radius, multiple bends, unloaded</b>	317.5 mm   12.5 in
<b>Minimum Bend Radius, single bend, unloaded</b>	185.42 mm   7.3 in
<b>Tensile Load, long term, maximum</b>	1,067.573 N   240 lbf
<b>Tensile Load, short term, maximum</b>	3,558.576 N   800 lbf
<b>Compression</b>	2.25 kg/mm   126 lb/in
<b>Compression Test Method</b>	FOTP-41
<b>Flex Test Method</b>	FOTP-104
<b>Impact</b>	4.34 ft lb   5.884 N-m
<b>Impact Test Method</b>	FOTP-25
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85

## Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)

# 760217505 | HEC-24SM-610M-AHF

---

<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-87-640   Telcordia GR-20   Telcordia GR-409
<b>Environmental Space</b>	Wireless installation

## Packaging and Weights

<b>Cable weight</b>	1,077.431 kg/km   724 lb/kft
---------------------	------------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Included Products

CS-8G-MP	-	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)
----------	---	--

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable