

760230439 | HEC-36MM-1806M5-AHFF

HELIAX® LazrSPEED® Hybrid Cable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable, copper and fiber
Product Brand	HELIAX® LazrSPEED®

General Specifications

Application	Remote radio head
Cable Type	Wireless feeder
Conductors, quantity	18
Construction Type	Shielded
Fiber Short Description	RFF-6 mm ²
Fiber Type, quantity	36
Fibers per Subunit, quantity	12
Inner Shield (Tape) Material	Corrugated aluminum
Jacket Color	Black
Outer Shield (Tape) Material	Fire retardant PE
Subunit, quantity	3
Total Fiber Count	36
Water Blocking Method	Water blocking tape(s) Water blocking threads


Dimensions

Buffer Tube/Subunit Diameter	4.572 mm 0.18 in
Diameter Over Jacket	31.75 mm 1.25 in
Conductor Gauge	6 mm ² class 5

Electrical Specifications

dc Resistance Note	Maximum value based on a standard condition of 20 °C (68 °F)
dc Resistance, maximum	3.301 ohms/km 1.006 ohms/kft

Representative Image



Material Specifications

Ripcord Material Para-aramid synthetic fiber

Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded	635 mm 25 in
Minimum Bend Radius, multiple bends, unloaded	381 mm 15 in
Minimum Bend Radius, single bend, unloaded	223.52 mm 8.8 in
Tensile Load, long term, maximum	800.68 N 180 lbf
Tensile Load, short term, maximum	2,668.932 N 600 lbf
Compression	2.25 kg/mm 126 lb/in
Compression Test Method	FOTP-41
Flex Test Method	FOTP-104
Impact	4.34 ft lb 5.884 N-m
Impact Test Method	FOTP-25
Twist	10 cycles
Twist Test Method	FOTP-85

Optical Specifications

Fiber Type OM2+, LazrSPEED® 150 | OM2+, LazrSPEED® 150

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)

760230439 | HEC-36MM-1806M5-AHFF

Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640 Telcordia GR-20 Telcordia GR-409
Environmental Space	Wireless installation

Packaging and Weights

Cable weight	1,579.537 kg/km 1,061.4 lb/kft
---------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5M-MP	-	LazrSPEED® 150 OM2+ Bend-Insensitive Multimode Fiber
----------	---	--

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable