CX8577-000 | NGF-CB3CR2V2082-SW



Next Generation Frame (NGF) Fiber Termination/Splice Block, preterminated, 96 LSH/APC, singlemode, right oriented, putty white

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Fiber patch/splice block

Product Series NGF

General Specifications

Functionality Patching | Splicing

Application Used in NGF-style frames only

Body Style Right orientation

Cable Exit Location Rear, bottom side

ColorPutty whiteColor, frontPutty white

Door Type, front Compression latch | Hinged

Growth ConfigurationFully loadedInterface, frontLSH/APC

Rack Type NGF
Shelf Movement Fixed
Total Ports, quantity 96

Dimensions

 Height
 558.8 mm | 22 in

 Width
 166.878 mm | 6.57 in

 Depth
 495.3 mm | 19.5 in

Material Specifications



CX8577-000 | NGF-CB3CR2V2082-SW

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C} \text{ to } +50 \,^{\circ}\text{C} \text{ (+23 °F to +122 °F)}$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

