

# 760188359 | 360G2-iP-1U-96F-LC-DM-TS-UHD

SYSTIMAX 360™ iPatch® InstaPATCH 1U 96F-LC Distribution Module, TeraSPEED, UHD Panel



## OBSOLETE

### Replaced By:

760188326 360G2-iP-1U-96F-LC-DM-TS-SD	SYSTIMAX 360™ iPatch® InstaPATCH 1U 96F-LC Distribution Module, TeraSPEED, Sliding Panel
760218404 HD-iP-1U-48F-LC-DM-TS-SD	HD iPATCH 1U 48F-LC Distribution Module, TeraSPEED, Sliding Panel

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber splice panel
<b>Product Brand</b>	SYSTIMAX 360™   iPatch®

## General Specifications

<b>Color</b>	Black
<b>Intelligence Type</b>	iPatch® enabled
<b>Interface, front</b>	LC/UPC
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	492.76 mm   19.4 in

## Material Specifications

**Material Type** Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -5 °C to +50 °C (+23 °F to +122 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** Austel | CE | CSA | UL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system

