

G2 2U Sliding Modular Cassette 8-slot Fiber Panel, unloaded



OBSOLETE

This product was discontinued on: June 30, 2022

Replaced By:

760251044
EPX-2U-MOD-ENC

EPX 2U sliding panel, accepts (8) G2 style splice cassettes, modules or adapter packs, providing up to 96 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Regional Availability Note	Discontinued in North America and Latin America regions. Optional replacements are 760209957 HD-2U (patch application) or 760231514 HD-2U-SP (splice application)
Portfolio	CommScope®
Product Type	Fiber patch panel

General Specifications

Application	Accepts eight G2 modular cassettes Accepts eight InstaPATCH® 360 data modules or 360DP panels Accepts two RoloSplices with four trays each
Interface, front	Unloaded
Rack Units	2
Shelf Movement	Sliding

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	457.2 mm 18 in

760193854 | 360G2-2U-MOD-SD

Packaging and Weights

Weight, net 5.443 kg | 12 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

