

NG4-VCKR2C470B1K



NG4access® Module VAM, CWDM, 4 channels, upgrade port, 1310 nm port, 2 circuits, LC/UPC, right, 1471 nm starting channel, 1 test port

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Brand	NG4access®
Product Series	NG4

General Specifications

Device Type	Plug-and-play module
Functionality	Multiplexing
Application	For use with NG4 access frames
Circuits, quantity	2
Distribution Type	4-channel CWDM
Interface, front	LC/UPC
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Multiplexers, quantity	2
Port Type, optional	1310 nm port Test port Upgrade port
Tray Orientation	Right orientation

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	130.3 mm 5.13 in

NG4-VCKR2C470B1K

Optical Specifications

Starting Channel Number	47
Starting Wavelength	1471 nm

Packaging and Weights

Packaging quantity	1
--------------------	---