

# NG4-VDML1MQA200C00



NG4access® Module VAM, DWDM, 40 channels, 100 GHz channel spacing, starting channel 20, 1 circuit, Mux, LC/APC, left, no test ports

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	DWDM module
<b>Product Brand</b>	NG4access®
<b>Product Series</b>	FACT   NG4
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications

<b>Device Type</b>	Plug-and-play module
<b>Functionality</b>	Multiplexing
<b>Application</b>	For use with NG4 access frames
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	40-channel DWDM
<b>Interface, front</b>	LC/APC
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Multiplexers, quantity</b>	1
<b>Tray Orientation</b>	Left orientation

## Dimensions

<b>Height</b>	13.21 mm   0.52 in
---------------	--------------------

# NG4-VDML1MQA200C00

---

**Width** 159.77 mm | 6.29 in

**Depth** 130.3 mm | 5.13 in

## Optical Specifications

**Channel Spacing** 100 GHz

**Starting Channel Number** 20

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

