

# NG4-VDMR2MDA280C1K



NG4access® Module VAM, DWDM, 8 channels, upgrade port, EXP port, 100 GHz channel spacing, starting channel 28, 2 circuits, Mux, LC/APC, right, 1 test port

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	DWDM module
Product Brand	NG4access®
Product Series	NG4

## General Specifications

Device Type	Plug-and-play module
Functionality	Multiplexing
Application	For use with NG4 access frames
Circuits, quantity	2
Distribution Type	8-channel DWDM
Interface, front	LC/APC
Interface, Input	LC/APC
Interface, Output	LC/APC
Multiplexers, quantity	2
Port Type, optional	Express port   Test port   Upgrade port
Tray Orientation	Right orientation

## Dimensions

Height	13.21 mm   0.52 in
Width	159.77 mm   6.29 in
Depth	130.3 mm   5.13 in

# NG4-VDMR2MDA280C1K

---

## Optical Specifications

Channel Spacing	100 GHz
Starting Channel Number	28

## Packaging and Weights

Packaging quantity	1
--------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

