

NGF-CB1MR2L1126



Next Generation Frame (NGF) Fiber Termination/Splice Block, pre-terminated, 144 SC/APC, singlemode, right oriented, putty white

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch/splice block
Product Series	NGF

General Specifications

Functionality	Patching Splicing
Application	Used in NGF-style frames only
Body Style	Right orientation
Cable Exit Location	Rear, bottom side
Color	Putty white
Color, front	Putty white
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	SC/APC
Rack Type	NGF
Shelf Movement	Fixed
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	144

Dimensions

Depth	434.34 mm 17.1 in
--------------	---------------------

Material Specifications

Finish	Powder coated
---------------	---------------

NGF-CB1MR2L1126

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

