



High Density 2U Sliding Fiber Splice Panel for holding up to 8 G2 modules (96 duplex LC ports) and Splice Wallet® / RoloSplice® / 360-LP-STACK splice tray kits (between 96 and 192 single fusion splices).

- The panel accommodates up to 8 G2 modules, providing up to 96 duplex LC ports
- The panel accommodates up to 96 single fusion splices when using the Splice Wallet® splice trays
- The panel accommodates up to 128 single fusion splices when using the RoloSplice® splice trays
- The panel accommodates up to 192 single fusion splices when using the 360-LP-STACK fusion splice trays

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	HD

General Specifications

Color	Black + Silver gray (front)
Intelligence Type	iPatch® ready
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	88.9 mm 3.5 in
Width	450.85 mm 17.75 in
Depth	501.65 mm 19.75 in

Material Specifications

Material Type	Steel
----------------------	-------

Environmental Specifications

Safety Standard UL 1863

Packaging and Weights

Packaging quantity 1

Weight, net 6.305 kg | 13.9 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

