


# RCP-47APU703125

---



RapidFiber® Termination Panel, 144-Position 4RU, singlemode, SC/UPC to stub, 31 m 25 in breakout

## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Regional Availability</b> | Latin America   North America       |
| <b>Portfolio</b>             | CommScope®                          |
| <b>Product Type</b>          | Fiber patch panel, with rapid cable |
| <b>Product Brand</b>         | RapidFiber®                         |
| <b>Product Series</b>        | RCP                                 |

## General Specifications

|                                  |   |
|----------------------------------|---|
| <b>Functionality</b>             | Patching                                      |
| <b>Body Style</b>                | Symmetrical                                   |
| <b>Cable Exit Location</b>       | Rear, left side                               |
| <b>Cable Stub Type</b>           | Indoor, microcable                            |
| <b>Color</b>                     | Putty white                                   |
| <b>Door Type, front</b>          | Hinged   Slide latch   Transparent            |
| <b>Growth Configuration</b>      | Fully loaded                                  |
| <b>Interface, front</b>          | SC/UPC  |
| <b>Interface, rear</b>           | Stub tail                                     |
| <b>Patch Cord Entry Location</b> | Front, left side   Front, right side          |
| <b>Rack Type</b>                 | EIA 19 in   EIA 23 in                         |
| <b>Rack Units</b>                | 4   |
| <b>Shelf Movement</b>            | Sliding                                       |
| <b>Total Fibers, quantity</b>    | 144   |
| <b>Total Ports, quantity</b>     | 144   |
| <b>Transmission Standards</b>    | IEC 60794-2   ISO/IEC 11801   TIA/EIA-568-B.3 |

## Dimensions


|               |                 |
|---------------|-----------------|
| <b>Height</b> | 177.8 mm   7 in |
|---------------|-----------------|

# RCP-47APU703125

|                     |                   |
|---------------------|-------------------|
| <b>Width</b>        | 482.6 mm   19 in  |
| <b>Depth</b>        | 381 mm   15 in    |
| <b>Cable Length</b> | 31 m   101.706 ft |

## Ordering Tree

RCP X - X X X X U X X X X X X X



ONLY FOR MULTIMODE VERSION.<sup>1</sup>  
 ONLY AVAILABLE IN RISER/PLENUM (P) CABLE TYPE<sup>2</sup>  
 RAPID PANEL IS DESIGNED AND QUALIFIED FOR UP TO 1000' (305 METERS) OF CABLE.<sup>3</sup>  
 ONLY AVAILABLE IN LC288 4RU<sup>4</sup>

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

## Optical Specifications

|                   |                       |
|-------------------|-----------------------|
| <b>Fiber Mode</b> | Singlemode            |
| <b>Fiber Type</b> | G.652.D   G.657.A2/B2 |

# RCP-47APU703125

---

## Environmental Specifications

|                                |  |
|--------------------------------|--|
| <b>Operating Temperature</b>   | -5 °C to +55 °C (+23 °F to +131 °F)  |
| <b>Storage Temperature</b>     | -40 °C to +70 °C (-40 °F to +158 °F)   |
| <b>Relative Humidity</b>       | 5%–85%, non-condensing   |
| <b>Qualification Standards</b> | NEBS Level 3   Telcordia GR-1435   Telcordia GR-326   Telcordia GR-409   UL 1863 |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

