

NG4-FR1000A1



NG4access® Fiber Skeleton Bay with integrated FOTSP

- Utilizes an industry-standard base frame and has six horizontal rear troughs and lower trough
- Has mounting positions for (6) NG4access 7-inch high chassis, which will hold up to 576 LC or 288 SC connections
- On the rear of the frame, a mounting location is available for a single splice chassis without sacrificing an available chassis position for standard chassis
- Includes a built-in jumper storage area on the left side for additional flexibility in cable routing
- The vertical cable guides and slack storage system are designed to accommodate up to 3,456 LC terminations

Product Classification

Regional Availability	Latin America North America
Product Type	Frame
Product Brand	NG4access®
Product Series	NG4

General Specifications

Access	Front Rear
Application	For use with NG4 panels
Color	Black
Growth Configuration	Unloaded
Mounting	Concrete floor Raised floor

Dimensions

Height	2,133.6 mm 84 in
Width	1,066.8 mm 42 in

Outline Drawing

NG4-FR1000A1

	Jumper Diameter (mm)	Cross Connect	Interconnect	Interconnect with FOTSP
SC/1728 Terminations	1.2	100%	100%	100%
	1.6	100%	100%	100%
	1.7	100%	100%	100%
	2.0	100%	78%	100%

LC/3456 Terminations	1.2	100%	100%	100%
	1.6	100%	61%	100%
	1.7	100%	54%	100%
	2.0	78%	39%	78%

Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Environmental Space Indoor

Qualification Standards Seismic rating, zone 4 | Telcordia GR-449-CORE

Packaging and Weights

Included Cable management

Packaging quantity 1

Packaging Type Crate | Pallet

Weight, net 541.136 kg | 1193 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

