

EH8723-000 | OCM1-CMB311L2



OCM1 LGX Fiber Optic Module, CWDM, Mux, LC/APC, 8 channels, upgrade port, starting wavelength 1310 nm

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Multiplexing
Technology Type	Thin film filter (TFF)
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, front	LC/APC
Interface, Input	LC/APC
Interface, Output	LC/APC
Multiplexers, quantity	1
Port Type, optional	Upgrade port

Dimensions

Height	129.54 mm 5.1 in
Width	27.94 mm 1.1 in
Depth	127 mm 5 in

Optical Specifications

Channel Spacing	20 nm
Starting Wavelength	1310 nm

Packaging and Weights

Packaging quantity 1
Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

