

SSC-760236114 | Radio Enclosure Pico for Nokia or Ericsson



Middle of Pole Pico Concealment Enclosure for Ericsson and Nokia Radios

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

SSC-760236114E1x

Up to (6) 2203/2205/2208/440x Radios

Up to (2) 220x/440x and (1) 4435 with separately ordered kit "860665179-AMK-002".

SSC-760236114E4x

(1) 4415/4426 Radio & (1) 220X/440x & (1) PSU AC 02/08

Or

(1) 8843 and (2) PSU-AC-02/08 with separate kit "860660900-1"

SSC-760236114N2x

Up to (4) AirScale Micro Radios

SSC-760236114N3x

(1) Nokia Dual Band 160W Radio & (1) AirScale Micro Radio or 1 AHFIB &

(1) DC Rectifier (Nokia FPAE OR Delta 1kW or 1.8kW)

Product Classification

Product Type	Mid pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Pure White Umbra Grey (RAL 7022)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	PSU-AC-08
Radio Compatibility, Ericsson	(1) 4415/4426 Radio & (1) 2203/2205/2208 & (1) PSU AC 08 220x 440x 4435 8843 Power Distribution

SSC-760236114 | Radio Enclosure Pico for Nokia or Ericsson

Radio Compatibility, Nokia (1) Airscale Dual Band 160W + (1) AirScale micro radio | AHFIA | AHFIB | Power Distribution | Up to (4) AirScale micro radios

Radios Included None

Dimensions

Height 1016 mm | 40 in

Width 401.32 mm | 15.8 in

Depth 304.8 mm | 12 in

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.125 m³ | 4.4 ft³

Weight (loaded) 36.287 kg | 80 lb

Weight (unloaded) 18.144 kg | 40 lb