

F2A-PDFPMDR

Base Product



FSJ2-50 SureFlex® Jumper with interface types 7-16 DIN Female Panel Mount and 7-16 DIN Male Right Angle, variable length

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Panel mount
Body Style, Connector B	Right angle
Interface, Connector A	7-16 DIN Female
Interface, Connector B	7-16 DIN Male
Orientation	0°
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Length	0 m 0 ft
Nominal Size	3/8 in

Electrical Specifications

DTF, Connector A	-32 dB
DTF, Connector B	-32 dB

Jumper Assembly Sample Label

F2A-PDFPMDR



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition