

CHGGG | IP06-24RUTP-PLUG-PLUG

Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP Riser Preterminated Copper Cable, RJ45 to RJ45, 24 links

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Copper trunk cable assembly |
| Product Brand | GigaSPEED XL® InstaPATCH® Cu |

General Specifications

| | |
|---------------------------------------|-------------------------------|
| ANSI/TIA Category | 6 |
| Cable Type | U/UTP (unshielded) |
| Conductor Type | Solid |
| Interface, Connector A | RJ45 plug |
| Interface Feature, connector A | Single row Standard density |
| Interface, Connector B | RJ45 plug |
| Interface Feature, connector B | Single row Standard density |
| Link Count | 24 |
| Wiring | T568B |

Dimensions

| | |
|---|---------|
| Cable Assembly Length Range (m) | 2 – 100 |
| Cable Assembly Length Range (ft) | 7 – 328 |

Electrical Specifications

| | |
|-------------------------------|---------|
| dc Resistance, maximum | 0.3 ohm |
| Safety Voltage Rating | 300 V |

Ordering Tree

CHGGG | IPO6-24RUTP-PLUG-PLUG

1 2 3 4 5 6 7 8 9 10 11 12
C A A A C - 1 1 H A B B F 0 5 0

| Cable Type | Connector B | Orientation A | Orientation B |
|---------------------------------------|--|-------------------------|-------------------------|
| A Cat 6A X10D – U/UTP (Plenum) | A Outlet* – Single Row Standard Density | 1 Trident Series Flat | 1 Trident Series Flat |
| B Cat 6A X10D – U/UTP (Riser) | B Outlet* – Dual Row Standard Density | 2 Right Paired Flat | 2 Right Paired Flat |
| C Cat 6A X10D – U/UTP (LSZH) | C Outlet* – Dual Row High Density | 3 Right Series Flat | 3 Right Series Flat |
| D Cat 6A X10D – F/UTP (Plenum) | G RJ45 Plug* – Single Row Standard Density | 4 Left Paired Flat | 4 Left Paired Flat |
| E Cat 6A X10D – F/UTP (Riser) | H RJ45 Plug* – Dual Row Standard Density | 5 Left Series Flat | 5 Left Series Flat |
| F Cat 6A X10D – F/UTP (LSZH) | J RJ45 Plug* – Dual Row High Density | 6 Trident Paired Flat | 6 Trident Paired Flat |
| G Cat 6 XL – U/UTP (Plenum) | N 1100 Module | A Trident Series Angled | A Trident Series Angled |
| H Cat 6 XL – U/UTP (Riser) | R 360 1100 Evolve Module | B Right Paired Angled | B Right Paired Angled |
| J Cat 6 XL – U/UTP (LSZH) | S OneLink 2x6 | C Right Series Angled | C Right Series Angled |
| K Cat 6A X10D – S/FTP (LSZH) | T OneLink 2x4 | D Left Paired Angled | D Left Series Angled |
| L Cat 6 – U/UTP Class B Rated (LSZH) | | E Left Series Angled | E Left Series Angled |
| M Cat 6A – U/UTP Class B Rated (LSZH) | | F Trident Paired Angled | F Trident Paired Angled |
| N Cat 6A X10D SD – U/UTP (Riser) | | | X Not Applicable |

| Connector A | Link | Outlet Color | UOM | Length |
|--|------|------------------|-----------|--------|
| A Outlet* – Single Row Standard Density | B 6 | 0 Not Applicable | 11 F Foot | 12 XXX |
| B Outlet* – Dual Row Standard Density | C 8 | 1 Black (BK) | M Meter | |
| C Outlet* – Dual Row High Density | D 12 | 2 Blue (BL) | | |
| G RJ45 Plug* – Single Row Standard Density | E 16 | 3 Blue (BL) | | |
| H RJ45 Plug* – Dual Row Standard Density | F 18 | 4 White (WH) | | |
| J RJ45 Plug* – Dual Row High Density | G 24 | | | |
| N 1100 Module | | | | |
| R 360 1100 Evolve Module | | | | |
| S OneLink 2x6 | | | | |
| T OneLink 2x4 | | | | |
| X Unterminated | | | | |

| Bundling | Jacket Color | Labeling |
|---------------|-----------------|-----------------|
| H Hook-n-loop | 8 White (WH) | A Generic Label |
| S Sleaving | 10 C Slate (SL) | |
| | Z Blue (BL) | |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Riser |
| Flammability Rating | UL 94 V-0 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



Included Products

| | |
|------------|---|
| 1071E-4/23 | – GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, 4 pair count |
|------------|---|

1071E-4/23



GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, 4 pair count

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Twisted pair cable |
| Product Brand | GigaSPEED XL® |
| Ordering Note | Not available in Europe, the Middle East, or Africa |

General Specifications

| | |
|--------------------------------|---|
| Product Number | 1071E |
| ANSI/TIA Category | 6 |
| Cable Component Type | Horizontal |
| Cable Type | U/UTP (unshielded) |
| Conductor Type, singles | Solid |
| Conductors, quantity | 8 |
| Pairs, quantity | 4 |
| Separator Type | Bisector |
| Transmission Standards | ANSI/TIA-568.2-D CENELEC EN 50288-6-1 ISO/IEC 11801 Class E |

Dimensions

| | |
|--------------------------------------|---------------------|
| Diameter Over Jacket, nominal | 5.893 mm 0.232 in |
| Jacket Thickness | 0.559 mm 0.022 in |
| Conductor Gauge, singles | 23 AWG |

Cross Section Drawing



Electrical Specifications

| | |
|--|---|
| dc Resistance Unbalance, maximum | 5 % |
| dc Resistance, maximum | 7.61 ohms/100 m 2.32 ohms/100 ft |
| Dielectric Strength, minimum | 1500 Vac 2500 Vdc |
| Mutual Capacitance at Frequency | 5.6 nF/100 m @ 1 kHz |
| Nominal Velocity of Propagation (NVP) | 69 % |
| Operating Frequency, maximum | 300 MHz |
| Operating Voltage, maximum | 80 V |
| Remote Powering | Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A |

Material Specifications

| | |
|----------------------------|-------------|
| Conductor Material | Bare copper |
| Insulation Material | Polyolefin |
| Jacket Material | PVC |
| Separator Material | Polyolefin |

Mechanical Specifications

1071E-4/23

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Non-plenum

Temperature Rating, UL 75 °C | 167 °F

Flame Test Method CMG | CMR

Packaging and Weights

Cable weight 38.097 kg/km | 25.6 lb/kft

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |