

FSJ4-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket (Halogen free jacketing non-fire-retardant)

#### **Product Classification**

 Product Type
 Coaxial wireless cable

 Product Brand
 HELIAX® | SureFlex®

**Product Series** FSJ4-50B

Ordering Note CommScope® standard product (Global)

General Specifications

**Product Number** 520093902/00 | SZ520093902/00

**Flexibility** Superflexible

Jacket Color Black

**Performance Note**Attenuation values typical, guaranteed within 5%

Dimensions

 Diameter Over Dielectric
 8.89 mm | 0.35 in

 Diameter Over Jacket
 13.462 mm | 0.53 in

 Inner Conductor OD
 3.556 mm | 0.14 in

 Outer Conductor OD
 12.192 mm | 0.48 in

Nominal Size 1/2 in

**Electrical Specifications** 

**Cable Impedance** 50 ohm ±1 ohm

**Capacitance** 82.7 pF/m | 25.207 pF/ft

dc Resistance, Inner Conductor2.69 ohms/km | 0.82 ohms/kftdc Resistance, Outer Conductor5.12 ohms/km | 1.561 ohms/kft

dc Test Voltage 2500 V

 $\label{eq:local_$ 

**COMMSCOPE®** 

**Insulation Resistance** 100000 MOhms-km

Jacket Spark Test Voltage (rms) 5000 V

Operating Frequency Band 1 – 10200 MHz

 Peak Power
 22.5 kW

 Velocity
 81 %

#### Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.327	0.1	22.5
1.5	0.401	0.122	22.5
2.0	0.463	0.141	22.5
10.0	1.044	0.318	10.14
20.0	1.485	0.453	7.12
30.0	1.828	0.557	5.79
50.0	2.377	0.724	4.45
85.0	3.13	0.954	3.38
88.0	3.187	0.971	3.32
100.0	3.406	1.038	3.11
108.0	3.546	1.081	2.98
150.0	4.214	1.285	2.51
174.0	4.558	1.389	2.32
200.0	4.908	1.496	2.16
204.0	4.96	1.512	2.13
300.0	6.095	1.858	1.74
400.0	7.121	2.17	1.49
450.0	7.592	2.314	1.39
460.0	7.684	2.342	1.38
500.0	8.042	2.451	1.32
512.0	8.148	2.483	1.3
600.0	8.891	2.71	1.19
700.0	9.683	2.951	1.09
800.0	10.431	3.179	1.01
824.0	10.605	3.232	1
894.0	11.101	3.383	0.95
960.0	11.555	3.522	0.92

Page 2 of 5

1000.0	11.824	3.604	0.89
1218.0	13.226	4.031	0.8
1250.0	13.423	4.091	0.79
1500.0	14.906	4.543	0.71
1700.0	16.027	4.885	0.66
1794.0	16.537	5.04	0.64
1800.0	16.57	5.05	0.64
2000.0	17.624	5.371	0.6
2100.0	18.137	5.528	0.58
2200.0	18.641	5.682	0.57
2300.0	19.138	5.833	0.55
2500.0	20.11	6.129	0.53
2700.0	21.056	6.418	0.5
3000.0	22.432	6.837	0.47
3400.0	24.198	7.375	0.44
3600.0	25.055	7.636	0.42
3700.0	25.478	7.765	0.42
3800.0	25.898	7.893	0.41
3900.0	26.314	8.02	0.4
4000.0	26.727	8.146	0.4
4100.0	27.136	8.271	0.39
4200.0	27.542	8.394	0.38
4300.0	27.946	8.517	0.38
4400.0	28.346	8.639	0.37
4500.0	28.744	8.761	0.37
4600.0	29.139	8.881	0.36
4700.0	29.531	9.001	0.36
4800.0	29.921	9.119	0.35
4900.0	30.308	9.238	0.35
5000.0	30.693	9.355	0.34
6000.0	34.427	10.493	0.31
8000.0	41.403	12.619	0.26
8800.0	44.054	13.427	0.24
10000.0	47.914	14.603	0.22

Material Specifications

COMMSCOPE°

**Dielectric Material** Foam PE

Jacket Material PE

Inner Conductor Material Copper-clad aluminum wire

Outer Conductor Material Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends31.75 mm1.25 inMinimum Bend Radius, single Bend31.75 mm1.25 in

Number of Bends, minimum20Number of Bends, typical50

 Tensile Strength
 79 kg | 174.165 lb

 Bending Moment
 2.7 N-m | 23.897 in lb

 Flat Plate Crush Strength
 2 kg/mm | 111.995 lb/in

### **Environmental Specifications**

Installation temperature-40 °C to +60 °C (-40 °F to +140 °F)Operating Temperature-55 °C to +85 °C (-67 °F to +185 °F)Storage Temperature-70 °C to +85 °C (-94 °F to +185 °F)

Attenuation, Ambient Temperature68 °F | 20 °CAverage Power, Ambient Temperature104 °F | 40 °CAverage Power, Inner Conductor Temperature212 °F | 100 °C

Packaging and Weights

**Cable weight** 0.21 kg/m | 0.141 lb/ft

#### Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant









