FEWL1LC42

Base Product



Singlemode LC/UPC Keyed Red to LC/UPC, Fiber Patch Cord, 1.6 mm Duplex, Riser

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Brand SYSTIMAX InstaPATCH® 360

Product Series FEW

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Connector A, quantity 2

Color, boot A Blue

Color, connector A Red

Connector B, quantity 2

Color, boot B Blue

Color, connector B Blue

Interface, Connector A LC/UPC

Interface Feature, connector A Keyed

Interface, Connector B LC/UPC

Jacket Color Yellow

Polarity Method B

Total Fibers, quantity 2

Dimensions

Cable Assembly Length Range (m) 1 - 999

Cable Assembly Length Range (ft) 1 - 999




FEWL1LC42

Diameter Over Jacket

1.6 mm | 0.063 in

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Riser

Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products



FEWL1LC42

460125206 760102780

SDC-LCR-16-KRD R-002-ZC-8W-F16

- TeraSPEED® Pre-Radiused LC Connector duplex for 1.6 mm Fiber, Singlemode
- TeraSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, duplex Singlemode, red
- Fiber indoor cable, TeraSPEED® 1.6mm Riser Zipcord, 2 fiber, Singlemode G.652.D and G.657.
 A1, Feet jacket marking



460125206

TeraSPEED® Pre-Radiused LC Connector duplex for 1.6 mm Fiber, Singlemode

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

Body StyleDuplexColorBlue

Ferrule Geometry Pre-radiused

Interface LC/UPC

Dimensions

 Length
 50.3 mm | 1.98 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.34 dBReturn Loss, minimum50 dB

Packaging and Weights



460125206

Packaging quantity

2

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



760102780 | SDC-LCR-16-KRD



TeraSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, duplex Singlemode, red

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector
Product Brand TeraSPEED®

General Specifications

Body Style Duplex
Color Red

 Ferrule Geometry
 Pre-radiused

 Interface
 LC/UPC

 Interface Feature
 Keyed

Dimensions

 Length
 52 mm | 2.047 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED® | OS2

Insertion Loss Change, mating 0.3 dB

COMMSCOPE®

760102780 | SDC-LCR-16-KRD

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, typical0.2 dBReturn Loss, minimum50 dB

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

 $\textbf{Insertion Loss Change, temperature} \quad \text{Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)}$



R-002-ZC-8W-F16

Fiber indoor cable, TeraSPEED® 1.6mm Riser Zipcord, 2 fiber, Singlemode G.652.D and G.657.A1, Feet jacket marking

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series R-ZC

General Specifications

Cable TypeCordageConstruction TypeNon-armoredSubunit TypeGel-freeJacket MarkingFeet


Total Fiber Count 2

Dimensions

 Height Over Jacket
 1.7 mm | 0.067 in

 Width Over Jacket
 3.5 mm | 0.138 in

Representative Image



Mechanical Specifications

COMMSCOPE®

R-002-ZC-8W-F16

Minimum Bend Radius, loaded38 mm | 1.496 inMinimum Bend Radius, unloaded15 mm | 0.591 inTensile Load, long term, maximum53 N | 11.915 lbfTensile Load, short term, maximum178 N | 40.016 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1, TeraSPEED®

Environmental Specifications

Installation temperature $-20 \, ^{\circ}\text{C}$ to $+70 \, ^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \, ^{\circ}\text{F}$)Operating Temperature $-20 \, ^{\circ}\text{C}$ to $+70 \, ^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \, ^{\circ}\text{F}$)Storage Temperature $-40 \, ^{\circ}\text{C}$ to $+70 \, ^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \, ^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Riser

Flame Test Listing NEC OFNR (ETL) and c(ETL)

Flame Test Method UL 1666

Environmental Test Specifications

Heat Age -20 °C to +85 °C (-4 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

COMMSCOPE®

R-002-ZC-8W-F16

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 5.8 kg/km | 3.897 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

