## MLOC-5-F1XM-XM-1M



HELIAX® M-LOC Multiport cluster 5 ports SureFlex® cable assembly with interface type M-LOC latching male to NEX10 male, size 1/4", length 1 meter

#### **Product Classification**

Product Type HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM

Product Brand HELIAX® | SureFlex®

Product Series MLOC

General Specifications

Attachment, Connector A Factory attached

Attachment, Connector B Factory attached

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector AM-LOC MaleInterface, Connector BNEX10 Male

Specification Sheet Revision Level A

**Dimensions** 

**Length** 1 m | 3.281 ft

Nominal Size 1/4 in

**Electrical Specifications** 

**3rd Order IMD Dynamic** -119 dBm

**3rd Order IMD Dynamic Test Method**Two +43 dBm carriers per IEC 62037

### VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000-3000 MHz	1.07	30	0.46
3000-4200 MHz	1.11	26	0.56
4200-5000 MHz	1.12	25	0.61

Mechanical Specifications



# MLOC-5-F1XM-XM-1M

Minimum Bend Radius, multiple Bends25.4 mm | 1 inMinimum Bend Radius, single Bend25.4 mm | 1 in

## **Environmental Specifications**

Installation temperature  $-40 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Operating Temperature  $-55 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-67 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Storage Temperature  $-55 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-67 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Immersion Test Method**Meets IEC 60529:2001, IP68 in mated condition

### Regulatory Compliance/Certifications

Classification
Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.andrew.com/ProductCompliance
Compliant
Compliant

