

F1A-PNMNF-2M

FSJ1-50A SureFlex® Jumper with interface types N Male and N Female,
2 m



Product Classification

| | |
|-----------------------|--------------------|
| Product Type | SureFlex® standard |
| Product Series | FSJ1-50A |

General Specifications

| | |
|---|----------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | N Male |
| Interface, Connector B | N Female |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|----------------|
| Length | 2 m 6.562 ft |
| Nominal Size | 1/4 in |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|-----------------------|-------------|-------------------------|
| 700–3000 MHz | 1.288 | 18 |

Jumper Assembly Sample Label

F1A-PNMNF-2M



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |



Included Products

| | |
|------------|--|
| 35422-33 | - Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket |
| 35422-75 | - Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket |
| FSJ1-50A | - FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket |
| FSJ1RK-50A | - FSJ1-50A, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a dO a1 Compliant |