

# F4S-HPHMDM-2-SGW



RSJ4-50 SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Male with HELIAX® SureGuard weatherproofing, 2 feet

- If there are threads along the entire device port length, the HELIAX® SureGuard weatherproofing solutions will only seal properly if the HSG-M29-ADPT adapter is installed on the device port

## Product Classification

<b>Product Type</b>	SureFlex® Premium, static PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	RSJ4-50

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	4.3-10 Male
<b>Interface, Connector B</b>	7-16 DIN Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	0.61 m   2.001 ft
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>3rd Order IMD Static</b>	-116 dBm
<b>3rd Order IMD Static Test Method</b>	Two +43 dBm carriers
<b>DTF, Connector A</b>	-34 dB
<b>DTF, Connector B</b>	-34 dB

## VSWR/Return Loss

Frequency Band	VSWR, typical	Return Loss, typical (dB)
698–960 MHz	1.065	30.04
1700–2200 MHz	1.065	30.04

# F4S-HPHMDM-2-SGW

2200–2700 MHz	1.106	25.96
3400–3800 MHz	1.222	20.01

## Jumper Assembly Sample Label



## Environmental Specifications

<b>Immersion Test Method</b>	Meets IEC 60529:2001, IP68 in mated condition
<b>Weatherproofing Method</b>	HELIAX® SureGuard weatherproofing boot

## Packaging and Weights

<b>Included</b>	Weatherproofing boot
-----------------	----------------------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

RSJ4-50	– RSJ4-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket
---------	---