

TFBM26-1



ION®-B Series Extension Unit for WiMAX 2600

OBSOLETE

Product Classification


Product Type	Extension unit
Product Brand	ION®-B

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	Medium

Dimension Drawing

TFBM26-1



Electrical Specifications



Impedance	50 ohm
License Band	WiMAX 2600
Voltage Range	85 to 265 Vac

Electrical Specifications, Tx (Downlink)

Operating Frequency Band	2496 – 2690 MHz (WiMAX 2600)
---------------------------------	------------------------------

Cabling Drawing

TFBM26-1



Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- TPSN1/28-80 – Power Supply Adapter ION®-B Series Remote Units, 80 W

TPSN1/28-80



Power Supply Adapter ION®-B Series Remote Units, 80 W

Product Classification

Product Type	Power adapters
Product Brand	ION®-B

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
-------------	--

Dimension Drawing

Electrical Specifications

Output Power, maximum	80 W
------------------------------	------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

