

ATC200-LITE-USB



Portable Controller

- Carried from site to site for RET antenna setup and optimization
- Supports up to 32 RET actuators operating in AISG 1.1 or 2.0 modes
- LED display indicates the presence of input power, output power, and data communication
- Equipped with USB and serial connectors
- Power supply efficiency is Energy Star® Level IV rated

Product Classification

Product Type RET controller

General Specifications

AISG Output Connector 8-pin DIN Female

AISG Output Connector Quantity 1

Auxiliary Interface USB

Color Gray | Yellow

Dimensions

Height 50.8 mm | 2 in

Width 127 mm | 5 in

Depth 76.2 mm | 3 in

Electrical Specifications

Input Voltage 110/240 Vac

Output Current at Voltage, continuous 3.0 A @ 24 V

Output Current at Voltage, maximum 3.0 A @ 24 V

Output Voltage, typical 24 V

Electrical Safety Standard CB | CE | IEC 60950-1

Interface Protocol Signal Data | dc

Power Supply dc Jack

Protocol AISG 1.1 | AISG 2.0

Material Specifications

Material Type Aluminum

ATC200-LITE-USB

Environmental Specifications

Operating Temperature -40 °C to +55 °C (-40 °F to +131 °F)
Relative Humidity Up to 95%, non-condensing

Packaging and Weights

Included Control unit | Power supply | Site configuration worksheet | US adapter | USB cable
Weight, net 0.4 kg | 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

