

# CV65CSX-M | CV65CSX-2X2



4-port sector antenna, 2x 790–960 and 2x 1710–2690 MHz, 65° HPBW, RET compatible

- Two DualPol® antennas under one radome
- Each antenna is independently capable of field adjustable electrical tilt
- Fully compatible with Andrew Teletilt® remote control system

## OBSOLETE

This product was discontinued on: **November 30, 2023**

Replaced By:

4P-2L2M-C2

4-port sector antenna, 2x 694–960 and 2x 1695–2690 MHz, 65°HPBW, 2x RET

## General Specifications

<b>Antenna Type</b>	Sector
<b>Band</b>	Multiband
<b>Color</b>	Light Gray (RAL 7035)
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Performance Note</b>	Outdoor usage   Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN
<b>Radome Material</b>	Fiberglass, UV resistant
<b>Radiator Material</b>	Copper   Low loss circuit board
<b>Reflector Material</b>	Aluminum
<b>RF Connector Interface</b>	7-16 DIN Female
<b>RF Connector Location</b>	Bottom
<b>RF Connector Quantity, high band</b>	2
<b>RF Connector Quantity, low band</b>	2
<b>RF Connector Quantity, total</b>	4

## Remote Electrical Tilt (RET) Information


<b>Model with Factory Installed AISG 2.0 Actuator</b>	CV65CSX-2X2
---	-------------

## Dimensions

# CV65CSX-M | CV65CSX-2X2

<b>Width</b>	301 mm   11.85 in
<b>Depth</b>	181 mm   7.126 in
<b>Length</b>	2453 mm   96.575 in
<b>Net Weight, without mounting kit</b>	21.2 kg   46.738 lb

## Array Layout




Bottom

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration

# CV65CSX-M | CV65CSX-2X2



## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	1710 – 2690 MHz   790 – 960 MHz
<b>Polarization</b>	±45°

## Electrical Specifications

Frequency Band, MHz	790–896	870–960	1710–1880	1850–1990	1920–2180	2300–2500	2500–2690
<b>Gain, dBi</b>	16.7	16.8	17.6	18	18.1	18.3	18.6
<b>Beamwidth, Horizontal, degrees</b>	63	62	70	67	67	56	60
<b>Beamwidth, Vertical, degrees</b>	8.1	7.6	5.6	5.3	5.1	4.4	4.1
<b>Beam Tilt, degrees</b>	0–10	0–10	2–12	2–12	2–12	2–12	2–12
<b>USLS (First Lobe), dB</b>	15	15	16	16	16	17	19
<b>Front-to-Back Ratio at 180°, dB</b>	30	30	27	28	23	27	30
<b>CPR at Boresight, dB</b>	27	25	19	20	20	16	19
<b>CPR at Sector, dB</b>	10	10	10	8	9	3	6
<b>Isolation, Cross Polarization, dB</b>	28	28	28	28	28	28	28
<b>Isolation, Inter-band, dB</b>	30	30	30	30	30	30	30

# CV65CSX-M | CV65CSX-2X2

<b>VSWR   Return loss, dB</b>	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
<b>PIM, 3rd Order, 2 x 20 W, dBc</b>	-150	-150	-150	-150	-150	-150	-150
<b>Input Power per Port, maximum, watts</b>	350	350	350	350	350	300	300

## Electrical Specifications, BASTA

<b>Frequency Band, MHz</b>	<b>790–896</b>	<b>870–960</b>	<b>1710–1880</b>	<b>1850–1990</b>	<b>1920–2180</b>	<b>2300–2500</b>	<b>2500–2690</b>
<b>Gain by all Beam Tilts, average, dBi</b>	16.3	16.3	17.2	17.6	17.6	17.9	18.1
<b>Gain by all Beam Tilts Tolerance, dB</b>	±0.4	±0.4	±0.5	±0.3	±0.5	±0.7	±0.4
<b>Gain by Beam Tilt, average, dBi</b>	0° 16.3 5° 16.4 10° 16.1	0° 16.4 5° 16.4 10° 16.1	2° 17.1 7° 17.3 12° 17.2	2° 17.5 7° 17.7 12° 17.5	2° 17.5 7° 17.7 12° 17.6	2° 17.9 7° 18.1 12° 17.6	2° 18.0 7° 18.2 12° 17.8
<b>Beamwidth, Horizontal Tolerance, degrees</b>	±2.2	±1.2	±4.4	±5.6	±5.6	±4.3	±5.2
<b>Beamwidth, Vertical Tolerance, degrees</b>	±0.4	±0.5	±0.3	±0.2	±0.3	±0.2	±0.2
<b>USLS, beampeak to 20° above beampeak, dB</b>	17	17	19	19	19	17	19
<b>Front-to-Back Total Power at 180° ± 30°, dB</b>	26	26	25	24	22	20	22
<b>CPR at Boresight, dB</b>	27	26	21	21	21	17	18
<b>CPR at Sector, dB</b>	13	13	12	9	9	5	6

## Mechanical Specifications

<b>Wind Loading @ Velocity, frontal</b>	396.0 N @ 150 km/h (89.0 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, lateral</b>	333.0 N @ 150 km/h (74.9 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, maximum</b>	762.0 N @ 150 km/h (171.3 lbf @ 150 km/h)
<b>Wind Loading @ Velocity, rear</b>	401.0 N @ 150 km/h (90.1 lbf @ 150 km/h)
<b>Wind Speed, maximum</b>	241 km/h (150 mph)

## Packaging and Weights

<b>Width, packed</b>	441 mm   17.362 in
<b>Depth, packed</b>	337 mm   13.268 in
<b>Length, packed</b>	2584 mm   101.732 in
<b>Weight, gross</b>	37.3 kg   82.232 lb

## Regulatory Compliance/Certifications

# CV65CSX-M | CV65CSX-2X2

---

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

- BSAMNT-OFFSET – Forward Offset Pipe Mounting Kit for 4.5 in (114.3 mm) OD round members

## \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

# BSAMNT-OFFSET



Forward Offset Pipe Mounting Kit for 4.5 in (114.3 mm) OD round members

## Product Classification

**Product Type** Pipe mounting kit

## General Specifications

**Application** Outdoor

**Color** Silver

## Dimensions

**Compatible Diameter, maximum** 114.3 mm | 4.5 in

**Compatible Diameter, minimum** 61 mm | 2.402 in

**Weight, net** 3.5 kg | 7.716 lb

## Material Specifications

**Material Type** Galvanized steel

## Packaging and Weights

**Included** Brackets | Hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# BSAMNT-OFFSET

---