

HR150



Heat Regenerated Dehydrator, 19 in rack mountable, 3.0 kPa (0.44 psig), with summary alarms, 48 Vdc (ac operation possible using optional power supply purchased separately)

OBSOLETE

This product was discontinued on: September 1, 2023

Product Classification

Product Type Dehydrator

General Specifications

Alarm Type	Summary
Cut In/Out Pressure Type	Continuous (default set to 3.0 kPa 0.4 psig)
Dehydrator Type	Automatically regenerating Desiccant
Dew Point	Better than -45 °C (-50 °F) at 95% RH at +40 °C (+104 °F)
Flow Rate, nominal	2.5 SLPM
High-Pressure Alarm	Factory set (default set to 4.5 kPa 0.7 psig)
Low-Pressure Alarm	Factory set (default set to 1.5 kPa 0.22 psig)
Mounting	Rack
Port Count	4
Port Type	3/8 in PE tube
Power Cord	dc power cord
Rack Type	EIA 19 in ETSI N3 (optional)
Rack Units	2
Regulated Output Pressure Type	Factory set, continuous

Dimensions


Product Height	91.8 mm 3.614 in
Product Width	439.4 mm 17.299 in
Product Depth	190.5 mm 7.5 in
Volume Capacity, maximum	0.6 m ³ 21.189 ft ³

HR150



HR150


Outline Drawing–Front



HR150 FRONT VIEW
DIMENSIONS ARE AS FOLLOWS: [] MILLIMETERS

HR150


Outline Drawing–Side



HR150 SIDE VIEW


HR150

Outline Drawing-Back



HR150

Outline Drawing–Top



HR150 TOP VIEW

Electrical Specifications

Alarm Contact Rating	Handles at least 0.5 A (ac or dc)
Power Consumption, maximum	45 W
Voltage	48–60 Vdc \pm 10%
Voltage Type	dc

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
------------------------------	-------------------------------------

Packaging and Weights

Weight, gross	9.6 kg 21.164 lb
Weight, net	4.8 kg 10.582 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

HR150

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

