

DBXLH-6565B-VTM | DBXLH-6565B-A2M



4-port sector antenna, 2x 824–960 and 2x 1710–2180 MHz, 65° HPBW, RET compatible

- Interleaved dipole technology providing for attractive, low wind load mechanical package

OBSOLETE

This product was discontinued on: November 30, 2023

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	PVC, UV resistant
Radiator Material	Aluminum
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, high band	2
RF Connector Quantity, low band	2
RF Connector Quantity, total	4

Remote Electrical Tilt (RET) Information


Model with Factory Installed AISG 2.0 Actuator	DBXLH-6565B-A2M
---	-----------------

Dimensions

Width	269 mm 10.591 in
Depth	132 mm 5.197 in
Length	1937 mm 76.26 in
Net Weight, without mounting kit	19 kg 41.888 lb

DBXLH-6565B-VTM | DBXLH-6565B-A2M

Array Layout



Array	Freq (MHz)	Conns
R1	824-960	1-2
B1	1710-2180	3-4

Bottom

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance

50 ohm

Operating Frequency Band

1710 – 2180 MHz | 824 – 960 MHz

DBXLH-6565B-VTM | DBXLH-6565B-A2M

Polarization

±45°

Electrical Specifications

Frequency Band, MHz	824–896	870–960	1710–1880	1850–1990	1920–2180
Gain, dBi	15	16.2	18	18.2	18.3
Beamwidth, Horizontal, degrees	70.8	67.7	69.3	64	58
Beamwidth, Vertical, degrees	11	10.6	4.9	4.6	4.4
Beam Tilt, degrees	0–10	0–10	0–6	0–6	0–6
USLS (First Lobe), dB	16	15	15	15	15
Front-to-Back Ratio at 180°, dB	30	30	32	32	32
CPR at Boresight, dB	22.6	21.4	20.8	18.1	15.9
CPR at Sector, dB	14.5	11.2	11.6	9	7.3
Isolation, Cross Polarization, dB	30	30	30	30	30
Isolation, Inter-band, dB	30	30	30	30	30
VSWR Return loss, dB	1.4 15.6	1.5 14.0	1.5 14.0	1.4 15.6	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150
Input Power per Port, maximum, watts	350	350	350	350	350

Electrical Specifications, BASTA

Frequency Band, MHz	824–896	870–960	1710–1880	1850–1990	1920–2180
Gain by all Beam Tilts, average, dBi	15.3	15.7	18	17.8	18.1
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.3	±0.3	±0.3	±0.6
Gain by Beam Tilt, average, dBi	0° 15.3 5° 15.3 10° 15.2	0° 15.7 5° 15.8 10° 15.7	0° 17.9 3° 18.0 6° 17.9	0° 17.7 3° 17.9 6° 17.7	0° 18.1 3° 18.2 6° 17.8
Beamwidth, Horizontal Tolerance, degrees	±2.1	±3.4	±3.6	±5.4	±7.4
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.6	±0.3	±0.2	±0.3
USLS, beampeak to 20° above beampeak, dB	16	17	14	13	14
Front-to-Back Total Power at 180° ± 30°, dB	20	20	26.7	25	24.6

DBXLH-6565B-VTM | DBXLH-6565B-A2M

Mechanical Specifications

Wind Loading @ Velocity, frontal	659.0 N @ 150 km/h (148.1 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	143.0 N @ 150 km/h (32.1 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	717.0 N @ 150 km/h (161.2 lbf @ 150 km/h)
Wind Speed, maximum	201 km/h (125 mph)

Packaging and Weights

Width, packed	376 mm 14.803 in
Depth, packed	267 mm 10.512 in
Length, packed	2250 mm 88.583 in
Weight, gross	27.6 kg 60.848 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 600899A-2 – Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance