

HBXX-6517DS-VTM | HBXX-6517DS-A2M



4-port sector antenna, 4x 1710–2180 MHz, 65° HPBW, RET compatible

- Superior azimuth tracking and pattern symmetry with excellent passive intermodulation suppression

OBSOLETE

This product was discontinued on: November 30, 2023

General Specifications

Antenna Type	Sector
Band	Single band
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	PVC, UV resistant
Radiator Material	Low loss circuit board
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, high band	4
RF Connector Quantity, total	4

Remote Electrical Tilt (RET) Information

Model with Factory Installed AISG 2.0 Actuator	HBXX-6517DS-A2M
---	-----------------

Dimensions

Width	305 mm 12.008 in
Depth	166 mm 6.535 in
Length	1906 mm 75.039 in
Net Weight, without mounting kit	18.5 kg 40.785 lb

Electrical Specifications

Impedance	50 ohm
------------------	--------

HBXX-6517DS-VTM | HBXX-6517DS-A2M

Operating Frequency Band	1710 – 2180 MHz
Polarization	±45°

Electrical Specifications

Frequency Band, MHz	1710–1880	1850–1990	1920–2180
Gain, dBi	19	19.1	19.2
Beamwidth, Horizontal, degrees	67	66.3	64.9
Beamwidth, Vertical, degrees	5	4.7	4.4
Beam Tilt, degrees	0–6	0–6	0–6
USLS (First Lobe), dB	18	18	18
Front-to-Back Ratio at 180°, dB	30	30	30
CPR at Boresight, dB	21	22	21
CPR at Sector, dB	10.3	11	9
Isolation, Cross Polarization, dB	30	30	30
VSWR Return loss, dB	1.4 15.6	1.4 15.6	1.4 15.6
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153
Input Power per Port, maximum, watts	350	350	350

Electrical Specifications, BASTA

Frequency Band, MHz	1710–1880	1850–1990	1920–2180
Gain by all Beam Tilts, average, dBi	18.5	18.6	18.8
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.3	±0.4
Gain by Beam Tilt, average, dBi	0° 18.4 3° 18.7 6° 18.4	0° 18.4 3° 18.7 6° 18.5	0° 18.7 3° 18.9 6° 18.6
Beamwidth, Horizontal Tolerance, degrees	±2.4	±1.7	±2.9
Beamwidth, Vertical Tolerance, degrees	±0.3	±0.3	±0.3
USLS, beampeak to 20° above beampeak, dB	18	19	19
Front-to-Back Total Power at 180° ± 30°, dB	25.2	25.9	26.3
CPR at Boresight, dB	22	23	22
CPR at Sector, dB	10	10	9

Mechanical Specifications

Wind Loading @ Velocity, frontal	668.0 N @ 150 km/h (150.2 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	175.0 N @ 150 km/h (39.3 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	777.0 N @ 150 km/h (174.7 lbf @ 150 km/h)

HBXX-6517DS-VTM | HBXX-6517DS-A2M

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

Width, packed 402 mm | 15.827 in

Depth, packed 292 mm | 11.496 in

Length, packed 2036 mm | 80.158 in

Weight, gross 28.2 kg | 62.17 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 600899A-2 – Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance