

14-port sector antenna, 2x 694–960, 4x 1695-2690 and 8x 2300–2690 MHz, 65° HPBW, 4x RET

- Combination of Tri-Band antenna and 2.4/2.6 GHz 8T8R beam forming antenna
- Internal SBT RET support via Calibration Port of 2.4/2.6 GHz array
- Optimized for Software Defined Split Six Sector applications on 2.4/2.6 GHz
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios

General Specifications

Antenna Type Sector

Band Multiband

Calibration Connector Interface 4.3-10 Female

Calibration Connector Quantity

Color Light Gray (RAL 7035)

Grounding TypeRF connector inner conductor and body grounded to reflector and

mounting bracket

Performance Note Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

Radome Material Fiberglass, UV resistant

Radiator Material Low loss circuit board

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, high band 12

RF Connector Quantity, mid band

RF Connector Quantity, low band

RF Connector Quantity, total

Remote Electrical Tilt (RET) Information

RET Hardware CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

RET Interface, quantity 2 female | 2 male

Input Voltage 10-30 Vdc



Page 1 of 7

Internal Bias Tee Cal Port

Internal RET High band (3) | Low band (1)

Power Consumption, idle state, maximum 1 W

Power Consumption, normal conditions, maximum 8 W

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions

Width 350 mm | 13.78 in

Depth 208 mm | 8.189 in

Length 2688 mm | 105.827 in

Net Weight, without mounting kit $$37.8\ \mathrm{kg} \ | \ 83.335\ \mathrm{lb}$$

TDD Column Spacing 58 mm | 2.283 in

Array Layout



Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	694-960	1-2	1	CPxxxxxxxxxxxxxxR1
Y1	2300-2690	3-4		
Y2	2300-2690	5-6	2	CPxxxxxxxxxxxxxY1
Y3	2300-2690	7-8	2	CPXXXXXXXXXXXXXXX
Y4	2300-2690	9-10		
Y5	1695-2690	11-12	3	CPxxxxxxxxxxxxxXY5
Y6	1695-2690	13-14	4	CPxxxxxxxxxxxxxY6

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration





Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1695 – 2690 MHz | 2300 – 2690 MHz | 694 – 960 MHz

Polarization ±45°

Total Input Power, maximum 900 W @ 50 °C

Electrical Specifications

	R1	R1	R1	Y1-Y4	Y1-Y4	Y5-Y6	Y5-Y6	Y5-Y6
Frequency Band, MHz	694-790	790-890	890-960	2300-250	0 2490-269	0 1695–192	0 1920-220	0 2300-2690
Gain, dBi	16.6	17	17.3	16.4	16.3	16.8	17.3	17.6
Beamwidth, Horizontal, degrees	68	67	65	94	95	62	61	63
Beamwidth, Vertical, degrees	8.4	7.5	6.9	5.7	5.3	7.3	6.5	5.5
Beam Tilt, degrees	0-10	0-10	0-10	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	17	19	20	16	17	16	18	21
Front-to-Back Ratio at 180°, dB	30	32	35	31	30	34	38	33
Coupling level, Amp, Antenna port to Cal port, dB				26	26			
Coupling level, max Amp Δ,				±2	±2			

Page 3 of 7



Antenna port to Cal port, dB								
Coupler, max Amp Δ , Antenna port to Cal port, dB				0.9	0.9			
Coupler, max Phase Δ, Antenna port to Cal port, degrees				7	7			
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28	28
Isolation, Inter-band, dB	30	30	30	20	20	30	30	30
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	250	250	250	150	150	200	200	150

Electrical Specifications, Broadcast 65°

Frequency Band, MHz	2300-2500	2490-2690
Gain, dBi	17.2	17.1
Beamwidth, Horizontal, degrees	62	62
Beamwidth, Horizontal Tolerance, degrees	±3.4	±3.7
Beamwidth, Vertical, degrees	5.7	5.3
Beamwidth, Vertical Tolerance, degrees	±0.4	±0.2
USLS (First Lobe), dB	17	17

Electrical Specifications, Service Beam

Frequency Band, MHz	2300-25	00 2490-2690
Steered 0° Gain, dBi	21.3	21.2
Steered 0° Gain Tolerance, dBi	±0.4	±0.5
Steered 0° Beamwidth, Horizontal, degrees	26	25
Steered 0° CPR over 10 dB Beamwidth, dB	18	19
Steered 0° Horizontal Sidelobe, dB	13	11
Steered 30° Gain, dBi	20.6	20.5
Steered 30° Gain Tolerance, dBi	±0.4	±0.6
Steered 30° Beamwidth,	27	26

Page 4 of 7



Horizontal, degrees

Steered 30° CPR over 10 dB 13 13

Beamwidth, dB

Electrical Specifications, Soft Split

Frequency Band, MHz 2300-2500 2490-2690

 Gain, dBi
 20.3
 20.3

 Beamwidth, Horizontal,
 31
 30

degrees

Horizontal Sidelobe, dB 21 19

Mechanical Specifications

Effective Projective Area (EPA), frontal $0.45 \text{ m}^2 \mid 4.844 \text{ ft}^2$ Effective Projective Area (EPA), lateral $0.38 \text{ m}^2 \mid 4.09 \text{ ft}^2$

Mechanical Tilt Range 0°-12°

 Wind Loading @ Velocity, frontal
 477.0 N @ 150 km/h (107.2 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 409.0 N @ 150 km/h (91.9 lbf @ 150 km/h)

 Wind Loading @ Velocity, maximum
 1,010.0 N @ 150 km/h (227.1 lbf @ 150 km/h)

 Wind Loading @ Velocity, rear
 506.0 N @ 150 km/h (113.8 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

 Width, packed
 460 mm | 18.11 in

 Depth, packed
 350 mm | 13.78 in

 Length, packed
 2830 mm | 111.417 in

 Weight, gross
 51.8 kg | 114.199 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted





Included Products

BSAMNT-4

Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.
 Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net6.5 kg | 14.33 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance ROHS Compliant UK-ROHS Compliant

