SD-003-KIT3



Static Desiccator Dehydrator, with remote mounting accessories kit

 To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. The compliant desiccant is orange when dry and turns green when saturated

OBSOLETE

This product was discontinued on: September 1, 2023

Product Classification

Product Type Dehydrator

General Specifications

Dehydrator Type Desiccant

Desiccant Capacity 283 liters (10 cu ft) at 80% RH, +20 °C

Mounting Pole
Port Count 1

Port Type 3/8 in PE tube x 1/8 NPT

Dimensions

 Product Height
 127 mm | 5 in

 Product Width
 50.8 mm | 2 in

 Product Depth
 50.8 mm | 2 in

 Volume Capacity, maximum
 0.028 m³ | 0.999 ft³

Volume Capacity, minimum 0 m³ | 0 ft³

Environmental Specifications

Operating Temperature -29 °C to +49 °C (-20 °F to +120 °F)

Packaging and Weights



SD-003-KIT3

 Height, packed
 86 mm | 3.386 in

 Width, packed
 165.1 mm | 6.5 in

 Depth, packed
 121.9 mm | 4.799 in

Included 1/4 in vinyl tubing | 90° elbow fitting | Instruction sheet | Polyethylene splice union

fitting | Static desiccator

 Weight, gross
 0.9 kg | 1.984 lb

 Weight, net
 0.2 kg | 0.441 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

