

2-port sector antenna, 2x 694–960 MHz, 65° HPBW, 1x RET

Utilizes RET-PMOD-A20-1A01

General Specifications

Antenna Type Sector

Band Single band

Grounding TypeRF connector body grounded to reflector and mounting bracket

Performance Note Outdoor usage

Radome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit board

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, high band 0
RF Connector Quantity, mid band 0
RF Connector Quantity, low band 2
RF Connector Quantity, total 2

Remote Electrical Tilt (RET) Information

RET Hardware CommRET v2

RET Interface 2x 8 pin connector as per IEC 60130-9 Daisy chain in: Male / Daisy chain

out: Female Pin3: RS485A(AISG_B), Pin5: RS485B(AISG_A), Pin6: DC

10~30V, Pin7: DC_ Return

RET Interface, quantity 1 female | 1 male

Input Voltage10-30 VdcInternal RETLow band (1)

 $\begin{array}{ll} \textbf{Power Consumption, idle state, maximum} & 2~\textrm{W} \\ \textbf{Power Consumption, normal conditions, maximum} & 10~\textrm{W} \\ \end{array}$

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions



2P-2L-C1

 Width
 320 mm | 12.598 in

 Depth
 140 mm | 5.512 in

 Length
 2500 mm | 98.425 in

 Net Weight, without mounting kit
 21 kg | 46.297 lb

Port Configuration



Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 694 – 960 MHz

 ${\bf Polarization} \hspace{2.5cm} \pm 45^{\circ}$ ${\bf Total Input Power, maximum} \hspace{2.5cm} 500 \ {\bf W}$

Electrical Specifications

Frequency Band, MHz	694-790	790-890	890-960
Gain, dBi	16.8	17.4	17.8
Beamwidth, Horizontal, degrees	69	66	63
Beamwidth, Vertical, degrees	8.9	7.8	7.2
Beam Tilt, degrees	3-12	3-12	3-12
USLS (First Lobe), dB	17	20	18

Page 2 of 3



2P-2L-C1

Front-to-Back Ratio, Copolarization 180° ± 30°, dB	31	33	31
Isolation, Cross Polarization, dB	28	28	28
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153
Input Power per Port, maximum, watts	300	300	300

Mechanical Specifications

0°-10° **Mechanical Tilt Range**

Wind Loading @ Velocity, frontal 418.0 N @ 150 km/h (94.0 lbf @ 150 km/h) Wind Loading @ Velocity, lateral 378.0 N @ 150 km/h (85.0 lbf @ 150 km/h) Wind Loading @ Velocity, rear 915.0 N @ 150 km/h (205.7 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

425 mm | 16.732 in Width, packed Depth, packed 235 mm | 9.252 in Length, packed 2780 mm | 109.449 in Weight, gross 30.6 kg | 67.461 lb

Regulatory Compliance/Certifications

Agency Classification CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant **UK-ROHS** Compliant



Included Products

Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. BSAMNT-B95-01

Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

