

# NNH4-65C-R6-V3



12-port sector antenna, 4x 698–896 and 8x 1695–2360 MHz, 65° HPBW, 6x RET

- Features broadband Low Band (698-896 MHz) and High Band (1695-2360 MHz) arrays for 4T4R (4X MIMO) capability for Band 14, AWS, PCS and WCS applications
- Independent tilt for all arrays
- Array configuration provides capability for 4T4R (4x MIMO) on Low band and Dual 4T4R (4x MIMO) on High band
- Optimized SPR performance across all operating bands
- Excellent wind loading characteristics
- The antenna is supplied with mounting kits that provide 0 degree of mechanical downtilt; optional downtilt mounting kits are available

## General Specifications

|   |  |
|---|--|
| <b>Antenna Type</b>                     | Sector   |
| <b>Band</b>                             | Multiband  |
| <b>Grounding Type</b>                   | RF connector inner conductor and body grounded to reflector and mounting bracket                                     |
| <b>Performance Note</b>                 | Outdoor usage   Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN |
| <b>Radome Material</b>                  | Fiberglass, UV resistant   |
| <b>Radiator Material</b>                | Low loss circuit board   |
| <b>Reflector Material</b>               | Aluminum   |
| <b>RF Connector Interface</b>           | 4.3-10 Female  |
| <b>RF Connector Location</b>            | Bottom   |
| <b>RF Connector Quantity, high band</b> | 8  |
| <b>RF Connector Quantity, mid band</b>  | 0  |
| <b>RF Connector Quantity, low band</b>  | 4  |
| <b>RF Connector Quantity, total</b>     | 12   |

## Remote Electrical Tilt (RET) Information

|                                |                                   |
|--------------------------------|-----------------------------------|
| <b>RET Hardware</b>            | CommRET v2                        |
| <b>RET Interface</b>           | 8-pin DIN Female   8-pin DIN Male |
| <b>RET Interface, quantity</b> | 1 female   1 male                 |
| <b>Input Voltage</b>           | 10–30 Vdc                         |


# NNH4-65C-R6-V3

|  |                              |
|--|------------------------------|
| <b>Internal RET</b>                                  | High band (4)   Low band (2) |
| <b>Power Consumption, idle state, maximum</b>        | 1 W                          |
| <b>Power Consumption, normal conditions, maximum</b> | 8 W                          |
| <b>Protocol</b>                                      | 3GPP/AISG 2.0 (Multi-RET)    |

## Dimensions

|   |                     |
|---|---------------------|
| <b>Width</b>                            | 498 mm   19.606 in  |
| <b>Depth</b>                            | 197 mm   7.756 in   |
| <b>Length</b>                           | 2438 mm   95.984 in |
| <b>Net Weight, without mounting kit</b> | 40.5 kg   89.287 lb |

## Array Layout




| Array | Freq (MHz) | Conns | RET (MRET) | AISG RET UID           |
|-------|------------|-------|------------|------------------------|
| R1    | 698-896    | 1-2   | 1          | CPxxxxxxxxxxxxxxxxmm.1 |
| R2    | 698-896    | 3-4   | 2          | CPxxxxxxxxxxxxxxxxmm.2 |
| Y1    | 1695-2360  | 5-6   | 3          | CPxxxxxxxxxxxxxxxxmm.3 |
| Y2    | 1695-2360  | 7-8   | 4          | CPxxxxxxxxxxxxxxxxmm.4 |
| Y3    | 1695-2360  | 9-10  | 5          | CPxxxxxxxxxxxxxxxxmm.5 |
| Y4    | 1695-2360  | 11-12 | 6          | CPxxxxxxxxxxxxxxxxmm.6 |

Left Bottom Right

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration

# NNH4-65C-R6-V3



## Electrical Specifications

|                                   |                                 |
|-----------------------------------|---------------------------------|
| <b>Impedance</b>                  | 50 ohm                          |
| <b>Operating Frequency Band</b>   | 1695 – 2360 MHz   698 – 896 MHz |
| <b>Polarization</b>               | ±45°                            |
| <b>Total Input Power, maximum</b> | 900 W @ 50 °C                   |

## Electrical Specifications

| Frequency Band, MHz                      | 698–806  | 806–896  | 1695–1880 | 1850–1990 | 1920–2180 | 2300–2360 |
|--|----------|----------|-----------|-----------|-----------|-----------|
| <b>Gain, dBi</b>                         | 15.6     | 15.8     | 16.7      | 17.1      | 17.5      | 18        |
| <b>Beamwidth, Horizontal, degrees</b>    | 73       | 72       | 60        | 62        | 62        | 58        |
| <b>Beamwidth, Vertical, degrees</b>      | 9.8      | 8.7      | 7.9       | 7.4       | 7         | 6.2       |
| <b>Beam Tilt, degrees</b>                | 0–10     | 0–10     | 0–10      | 0–10      | 0–10      | 0–10      |
| <b>USLS (First Lobe), dB</b>             | 23       | 18       | 17        | 18        | 19        | 18        |
| <b>Front-to-Back Ratio at 180°, dB</b>   | 29       | 31       | 37        | 39        | 38        | 36        |
| <b>Isolation, Cross Polarization, dB</b> | 25       | 25       | 25        | 25        | 25        | 25        |
| <b>Isolation, Inter-band, dB</b>         | 25       | 25       | 25        | 25        | 25        | 25        |
| <b>VSWR   Return loss, dB</b>            | 1.5 14.0 | 1.5 14.0 | 1.5 14.0  | 1.5 14.0  | 1.5 14.0  | 1.5 14.0  |

# NNH4-65C-R6-V3

|   |      |      |      |      |      |      |
|---|------|------|------|------|------|------|
| <b>PIM, 3rd Order, 2 x 20 W, dBc</b>                | -150 | -150 | -150 | -150 | -150 | -150 |
| <b>Input Power per Port at 50°C, maximum, watts</b> | 300  | 300  | 250  | 250  | 250  | 200  |

## Mechanical Specifications

|   |   |
|---|---|
| <b>Effective Projective Area (EPA), frontal</b> | 0.9 m <sup>2</sup>   9.688 ft <sup>2</sup>  |
| <b>Effective Projective Area (EPA), lateral</b> | 0.31 m <sup>2</sup>   3.337 ft <sup>2</sup> |
| <b>Mechanical Tilt Range</b>                    | 0°–10°                                      |
| <b>Wind Loading @ Velocity, frontal</b>         | 954.0 N @ 150 km/h (214.5 lbf @ 150 km/h)   |
| <b>Wind Loading @ Velocity, lateral</b>         | 331.0 N @ 150 km/h (74.4 lbf @ 150 km/h)    |
| <b>Wind Loading @ Velocity, maximum</b>         | 1,235.0 N @ 150 km/h (277.6 lbf @ 150 km/h) |
| <b>Wind Loading @ Velocity, rear</b>            | 785.0 N @ 150 km/h (176.5 lbf @ 150 km/h)   |
| <b>Wind Speed, maximum</b>                      | 241 km/h (150 mph)                          |

## Packaging and Weights

|                       |                      |
|-----------------------|----------------------|
| <b>Width, packed</b>  | 565 mm   22.244 in   |
| <b>Depth, packed</b>  | 309 mm   12.165 in   |
| <b>Length, packed</b> | 2625 mm   103.347 in |
| <b>Weight, gross</b>  | 53.2 kg   117.286 lb |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |




## Included Products

|           |   |  |
|-----------|---|--|
| BSAMNT-2F | – | Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications. |
|-----------|---|--|

## \* Footnotes

|                         |   |
|-------------------------|---|
| <b>Performance Note</b> | Severe environmental conditions may degrade optimum performance |
|-------------------------|---|

# BSAMNT-2F



Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

## Product Classification

**Product Type** Fixed tilt mounting kit

## General Specifications

**Application** Outdoor

**Color** Silver

## Dimensions

**Compatible Diameter, maximum** 115 mm | 4.528 in

**Compatible Diameter, minimum** 60 mm | 2.362 in

**Weight, net** 3.8 kg | 8.378 lb

## Material Specifications

**Material Type** Galvanized steel

## Packaging and Weights

**Included** Brackets | Hardware

**Packaging quantity** 1

**Weight, gross** 4 kg | 8.818 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CE            | Compliant with the relevant CE product directives  |
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

# BSAMNT-2F

---

