

PULSAR-EDGE-C2



PowerShift® High Power Pulsar Edge Controller with C2 software
(included with shelf)

Product Classification

Product Type	Module
Product Brand	PowerShift®
Product Series	V2

General Specifications

Backplane Interfaces	10/100 Base-T Ethernet One Galaxy Protocol (GP) RS485 bus
Front Panel Display	Interface to shelf mounted interactive display

Dimensions

Height	41.402 mm 1.63 in
Width	18.288 mm 0.72 in
Depth	345.44 mm 13.6 in

Electrical Specifications

Electrical Safety Standard	UL60950-UL/cUL with CB report
-----------------------------------	-------------------------------

Environmental Specifications

Relative Humidity	95%, non-condensing
Ambient Temperature	-40 °C -40 °F 65 °C 149 °F
Mean Time Between Failures (MTBF) at Temperature	300,000 h @ 25 °C

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

PULSAR-EDGE-C2

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

