

12-port sector antenna, 4x 694–960, 4x 1427–2690 and 4x 1695-2690 MHz, 65° HPBW, 6x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios

General Specifications

Antenna Type	Sector
Band	Multiband
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN
Radome Material	Fiberglass, UV resistant
Radiator Material	Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	4
RF Connector Quantity, total	12

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	2 female 2 male
Input Voltage	10-30 Vdc
Internal RET	High band (4) Low band (2)
Power Consumption, idle state, maximum	1 W
Power Consumption, normal conditions, maximum	8 W
Protocol	3GPP/AISG 2.0 (Single RET)



Dimensions

Width	498 mm 19.606 in
Depth	197 mm 7.756 in
Length	1848 mm 72.756 in
Net Weight, without mounting kit	37.5 kg 82.673 lb

Array Layout



Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	694-960	1-2	1	CPxxxxxxxxxxxxxR1
R2	694-960	3-4	2	CPxxxxxxxxxxxxxR2
Y1	1695-2690	5-6	3	CPxxxxxxxxxxxxXXXXXXXXXXY1
Y2	1427-2690	7-8	4	CPxxxxxxxxxxxxXXXXXXXXXY2
Y3	1427-2690	9-10	5	CPxxxxxxxxxxxxxXXXXXXXXXY3
Y4	1695-2690	11-12	6	CPxxxxxxxxxxxxxXXXXY4

Left Right Bottom


(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration





Logo Image



Electrical Specifications

Impedance 50 of	Im
Operating Frequency Band 1427	– 2690 MHz 1695 – 2690 MHz 694 – 960 MHz
Polarization ±45°	
Total Input Power, maximum900	V @ 50 °C
Floctrical Capacifications	

Electrical Specifications

R1&R2	R1&R2	R1&R2	Y1&Y4	Y1&Y4	Y2&Y3	Y2&Y3	Y2&Y3	

Page 3 of 5



RRZZVV-65B-R6H4

Frequency Band, MHz	694-790	790-890	890-960	1695-220	0 2300-2690	0 1427-1518	3 1695-2200) 2300-2690
Gain, dBi	14.3	14.6	14.7	17.9	18.3	15.9	17.6	17.9
Beamwidth, Horizontal, degrees	70	65	63	64	57	65	62	60
Beamwidth, Vertical, degrees	11.5	10.3	9.3	6.4	5	8.6	6.8	5.1
Beam Tilt, degrees	2-14	2-14	2-14	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	17	17	17	17	18	20	16	16
Front-to-Back Ratio at 180°, dB	34	30	27	32	29	34	34	31
Isolation, Cross Polarization, dB	27	27	27	27	27	26	26	27
Isolation, Inter-band, dB	27	27	27	27	27	27	27	27
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	300	300	300	250	200	250	250	200

Mechanical Specifications

Wind Loading @ Velocity, frontal	694.0 N @ 150 km/h (156.0 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	235.0 N @ 150 km/h (52.8 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	900.0 N @ 150 km/h (202.3 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	571.0 N @ 150 km/h (128.4 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	368 mm 14.488 in
Length, packed	2034 mm 80.079 in
Weight, gross	52.4 kg 115.522 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Page 4 of 5



RRZZVV-65B-R6H4



Included Products

BSAMNT-3

Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



