

# 137SEM

---



Fixed-tuned PDR40 for elliptical waveguide 37

## Product Classification

**Product Type** Elliptical waveguide connector

## General Specifications

**Attachment Method** Tab-flare | Tool-flare

**Body Style** Straight, fixed-tuned

**Inner Contact Plating** Unplated

**Interface** PDR40

**Outer Contact Plating** Unplated

**Pressurizable** Yes

## Dimensions

**Width** 117.602 mm | 4.63 in

**Length** 165.608 mm | 6.52 in

**Transition Length** 108.204 mm | 4.26 in

**Waveguide Size** WR229 | WG11 | R40

## Electrical Specifications

**Insertion Loss, typical** 0.01 dB

**Operating Frequency Band** 3.4 – 4.2 GHz

**Peak Power at Frequency, maximum** 309.00 kW @ 4.00 GHz

## Material Specifications

**Material Type** Brass

## Environmental Specifications

**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

# 137SEM

---

## Packaging and Weights

**Weight, net**

3 kg | 6.614 lb

## Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.andrew.com/ProductCompliance](http://www.andrew.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

**Insertion Loss, typical** 0.05√freq (GHz) (not applicable for elliptical waveguide)