


# MLOC-5-FIXM-HM-5M



HELIAX® M-LOC Multiport cluster 5 ports SureFlex® cable assembly with interface type M-LOC latching male to 4.3-10 male, size 1/4", length 5 meters

## Product Classification

<b>Product Type</b>	HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	MLOC

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	M-LOC Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	5 m   16.404 ft
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-119 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000–3000 MHz	1.07	30	1.89
3000–4200 MHz	1.11	26	2.28

# MLOC-5-FIXM-HM-5M

---

4200–5000 MHz

1.12

25

2.51

## Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 25.4 mm | 1 in

**Minimum Bend Radius, single Bend** 25.4 mm | 1 in

## Environmental Specifications

**Installation temperature** -40 °C to +60 °C (-40 °F to +140 °F)

**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

Compliant

