


# E11F05P98



Diplexer, DCS 1800/UMTS 2100, AISG compatible, dc pass on UMTS port

- Industry leading PIM performance
- Designed for network Modernization, introduction of LTE1800 on existing site
- Designed for network Modernization, introduction of UMTS2100 on existing site
- dc/AISG pass-through on high frequency ports

## OBSOLETE

This product was discontinued on: July 1, 2022

### Replaced By:

E14F06P32

Ultra Compact Single Diplexer 1350-1880/1920-2690, 4.3-10 connectors

## Product Classification

**Product Type** Diplexer

## General Specifications

**Product Family** CBC1821  
**Color** Gray  
**Common Port Label** PORT 3 COMMON  
**Modularity** 1-Single  
**Mounting** Pole | Wall  
**Mounting Pipe Hardware** Band clamps (2)  
**RF Connector Interface** 7-16 DIN Female  
**RF Connector Interface Body Style** Long neck

## Dimensions

**Height** 149 mm | 5.866 in  
**Width** 145 mm | 5.709 in  
**Depth** 42 mm | 1.654 in  
**Mounting Pipe Diameter Range** 40–160 mm

## Electrical Specifications

**Impedance** 50 ohm

# E11F05P98

License Band, Band Pass DCS 1800 | IMT 2100

## Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through, combiner	Branch 2
dc/AISG Pass-through, demultiplexer	Branch 2
Lightning Surge Current	3 kA
Lightning Surge Current Waveform	10/350 waveform


## Electrical Specifications

Sub-module	1	1
Branch	1	2
Port Designation	PORT 2 1710-1880	Port 1 1920-2170
License Band	DCS 1800, Band Pass IMT 2100, Band Pass	

## Electrical Specifications, Band Pass

Frequency Range, MHz	1710–1880	1920–2170
Insertion Loss, typical, dB	0.15	0.25
Return Loss, minimum, dB	18	18
Return Loss, typical, dB	20	20
Isolation, minimum, dB	50	50
Input Power, RMS, maximum, W	250	250
3rd Order PIM, typical, dBc	-161	
3rd Order PIM Test Method	Two +43 dBm carriers	
7th Order PIM, typical, dBc		-168
7th Order PIM Test Method		Two +43 dBm carriers

## Block Diagram



## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Corrosion Test Method</b>	IEC 60068-2-11, 30 days
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Volume</b>	0.9 L
<b>Weight, net</b>	2 kg   4.409 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



