

# LS2-HRHR-D

---

## Base Product



D-CLASS LSF2-50 SureFlex® Jumper with interface types 4.3-10 Male Right Angle and 4.3-10 Male Right Angle, variable length

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

|                       |                                      |
|-----------------------|--------------------------------------|
| <b>Product Type</b>   | Wireless transmission cable assembly |
| <b>Product Series</b> | LSF2-50                              |

## General Specifications

|   |  |
|---|--|
| <b>Body Style, Connector A</b>            | Right angle  |
| <b>Body Style, Connector B</b>            | Right angle  |
| <b>Interface, Connector A</b>             | 4.3-10 Male  |
| <b>Interface, Connector B</b>             | 4.3-10 Male  |
| <b>Specification Sheet Revision Level</b> | A  |
| <b>Variable Length</b>                    | For custom lengths, contact your local ANDREW representative |

## Dimensions

|                     |        |
|---------------------|--------|
| <b>Nominal Size</b> | 3/8 in |
|---------------------|--------|

## Logo Image

# LS2-HRHR-D



## Electrical Specifications

|  |                                    |
|--|------------------------------------|
| <b>3rd Order IMD Dynamic</b>             | -119 dBm                           |
| <b>3rd Order IMD Dynamic Test Method</b> | Two +43 dBm carriers per IEC 62037 |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698–970 MHz    | 1.065 | 30.04            |
| 1700–2200 MHz  | 1.065 | 30.04            |
| 2200–2700 MHz  | 1.083 | 27.99            |
| 3400–3800 MHz  | 1.222 | 20.01            |
| 4000–6000 MHz  | 1.222 | 20.01            |

## Jumper Assembly Sample Label

# LS2-HRHR-D

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition