# CMAX-0US1-UW43-I53



Cell-Max<sup>™</sup> Low PIM Omni In-building Antenna, 617-960, 1400-1600, 1695-2700 MHz, 3300-4200 MHz and 4900-6000MHz 4.3-10, Not recommended for metal ceilings

### **Product Classification**

**Product Type** In-building antenna

**Product Brand** Cell-Max™

### General Specifications

**Application** Indoor **Antenna Type** Omni **Polarization** Horizontal Color White

Mounting Thru-hole ceiling mount (optional)

**Mounting Note** For antenna installation on metal ceilings, please contact your local ANDREW representative

**Radome Material** ABS

**RF Connector Interface** 4.3-10 Female

Dimensions

Height 18 mm | 0.709 in **Outer Diameter** 220 mm | 8.661 in

### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1400 - 1500 MHz | 1695 - 2700 MHz | 3300 - 4200 MHz | 4900 - 6000 MHz | 617 - 698

MHz | 698 - 960 MHz

**Electrical Note** Values typical, unless otherwise stated

### **Electrical Specifications**

Frequency Band, MHz	617-698	698-960	1400-1500	1695-2700	3300-4200	4900-6000
Gain, dBi	4.6	4.8	5.4	5.5	5.5	5.4
Beamwidth, Horizontal, degrees	360	360	360	360	360	360

Page 1 of 2

## CMAX-OUS1-UW43-I53

VSWR   Return loss, dB	1.6   12.7	1.6   12.7	1.6   12.7	1.6   12.7	1.6   12.7	1.6   12.7
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	100	100	100	100	100	100

### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Relative Humidity** Up to 100%

## Packaging and Weights

 Height, packed
 93 mm | 3.661 in

 Depth, packed
 227 mm | 8.937 in

 Length, packed
 225 mm | 8.858 in

Packaging quantity

 Weight, gross
 0.46 kg | 1.014 lb

 Weight, net
 0.3 kg | 0.661 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ROHS Compliant UK-ROHS Compliant

