


# FE-12104-G-R4



HELIAX® Fiber and Power Junction Box for 1 Hybrid Trunk / 4 Hybrid Jumper Cables with Internal Grounding

**OBSOLETE**

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Outdoor junction box
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Application</b>	Used as a fiber/power junction box
<b>Cable Entry, quantity, maximum, bottom</b>	5
<b>Color</b>	Gray
<b>Fiber System Configuration Type</b>	Hybrid with junction box, 4 RRU
<b>Mounting</b>	Pipe, 44–114 mm (1.75–4.5 in) OD   Wall

## Dimensions

<b>Height</b>	317.5 mm   12.5 in
<b>Width</b>	266.7 mm   10.5 in
<b>Depth</b>	101.6 mm   4 in
<b>Cable Entry Fiber Gland Size, maximum</b>	25 mm   0.984 in
<b>Cable Entry Fiber Gland Size, minimum</b>	18 mm   0.709 in
<b>Cable Entry Jumper Gland Size, maximum</b>	18 mm   0.709 in
<b>Cable Entry Jumper Gland Size, minimum</b>	13 mm   0.512 in
<b>Compatible Center Conductor Gauge</b>	10 AWG   12 AWG

## Material Specifications

<b>Material Type</b>	High-impact polycarbonate, UV resistant
----------------------	---

# FE-12104-G-R4

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Environmental Space</b>	Indoor   Outdoor
<b>Qualification Standards</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Included</b>	Mounting kit
<b>Weight, net</b>	1.579 kg   3.48 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

