# FPX-2FS7/04AU046



FPX Fiber Optic Termination Panel with IFC Stranded Cable, 2RU, 19in, Singlemode, 48 fiber, SC/UPC connectors, Stub tail at far end, putty white, 46m

## Product Classification

Depth

| Regional Availability            | Latin America   North America     |
|----------------------------------|-----------------------------------|
| Portfolio                        | CommScope®                        |
| Product Type                     | Fiber patch panel, with OSP cable |
| Product Series                   | FPX                               |
| General Specifications           |                                   |
| Functionality                    | Patching                          |
| Adapter Packs Included, quantity | 4                                 |
| Body Style                       | Symmetrical                       |
| Cable Exit Location              | Upward                            |
| Cable Stub Type                  | OSP                               |
| Color                            | Putty white                       |
| Color, front                     | Putty white                       |
| Growth Configuration             | Fully loaded                      |
| Interface, front                 | SC/UPC                            |
| Interface, rear                  | Stub tail                         |
| Patching Capacity, maximum       | 48                                |
| Rack Type                        | EIA 19 in   EIA 23 in             |
| Rack Units                       | 2                                 |
| Shelf Movement                   | Sliding                           |
| Total Fibers, quantity           | 48                                |
| Total Ports, quantity            | 48                                |
| Dimensions                       |                                   |
| Height                           | 88.9 mm   3.5 in                  |
| Width                            | 482.6 mm   19 in                  |
|                                  |                                   |

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023

304.8 mm | 12 in




# FPX-2FS7/04AU046

#### **Cable Length**

46 m | 150.919 ft

## Ordering Tree



### Material Specifications

| Finish                 | Powder coated |
|------------------------|---------------|
| Material Type          | Steel         |
| Optical Specifications |               |
| Fiber Mode             | Singlemode    |

### **Environmental Specifications**

**Operating Temperature** 

-40 °C to +85 °C (-40 °F to +185 °F)

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023



# FPX-2FS7/04AU046

Storage Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

Packaging quantity

# Regulatory Compliance/Certifications

| Agency     | Classification  |
|------------|---|
| CHINA-ROHS | Below maximum concentration value                                     |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS       | Compliant   |
| UK-ROHS    | Compliant   |
|            |   |

1

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 12, 2023

