CELLMAX-0-43-WI



Cell-Max TM Omni In-building Antenna, 698–960 MHz ,1695–2700 MHz and 3100-4200MHz

• This product is part of the ANDREW Wired for Wireless® Solution

Product Classification

Product Type In-building antenna

Product Brand Cell-Max™

General Specifications

ApplicationIndoorAntenna TypeOmniAntenna Array CharacteristicSISOPolarizationVertical

Color White (RAL 9016)

Mounting Thru-hole ceiling mount (optional)

Number of Ports

Pigtail Cable670-141SXE, plenum ratedRadome MaterialASA+PC, UV stabilized

RF Connector Interface 4.3-10 Female

Dimensions

 Height
 85 mm | 3.346 in

 Pigtail Length
 500 mm | 19.685 in

 Outer Diameter
 186 mm | 7.323 in

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1710 – 2700 MHz | 3100 – 4200 MHz | 698 – 960 MHz

Electrical Note Values typical, unless otherwise stated

Electrical Specifications

Frequency Band, MHz 698-960 1695-2700 3100-4200

Page 1 of 2



CELLMAX-0-43-WI

Gain, dBi	2.5	5.8	7.1
Beamwidth, Horizontal, degrees	360	360	360
PIM, 3rd Order, 2 x 20 W, dBc	-140	-140	-140
Input Power per Port, maximum, watts	100	100	100

VSWR/Return Loss

Frequency Band	VSWR, Maximum	Return Loss, Maximum (dB)	VSWR, Mean	Return Loss, Mean (dB)
698-960 MHz	1.603	12.7	1.398	15.6
1695-2700 MHz	1.603	12.7	1.398	15.6
3100-4200 MHz	1.603	12.7	1.398	15.6

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Packaging and Weights

 Height, packed
 135 mm | 5.315 in

 Width, packed
 195 mm | 7.677 in

 Length, packed
 195 mm | 7.677 in

Packaging quantity 1

 Weight, gross
 0.4 kg | 0.882 lb

 Weight, net
 0.3 kg | 0.661 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ROHS Compliant UK-ROHS Compliant



