

# ARRIS IP815

## Media Player



### PRODUCT OVERVIEW:

Extend the power of the ARRIS Whole Home Solution to any room in your house with the ARRIS IP815 Media Player. The IP815 is enabled with MoCA 2.0 and 802.11ac Wi-Fi home networking to receive live, recorded, OTT, and Video-On-Demand content from the DCX3635 Media Gateway. The Whole Home Solution enables a full DVR experience in every room equipped with an IP815, including a Live Time-Shift Buffer. With an IP815 connected to the home network, end users can browse the DVR recordings stored on the media gateway, watch the recorded content, or schedule future recordings.

---



## FEATURES

- Industry-standard video, audio, and data outputs (for details, refer to Specifications)
- Supports standard and high-definition MPEG-2 and MPEG-4 formats, including full 1080p60 HDTV decode
- True 1080p high-definition playback
- Embedded IP networking over coaxial cable with integrated MoCA 2.0
- Two-way IP data communication
- Integrated 802.11ac Wi-Fi with internal 3x3 MIMO antenna array and 5GHz radio
- Default Wi-Fi security: WPA-PSK WEP-64/128, WPA, WPA2
- Powerful (MIPS) RISC processor
- Dolby® 5.1 (all Outputs) and Dolby Digital Plus 7.1 digital audio (HDMI only)
- IR and RF4CE remote control interfaces
- Power and Home LAN LEDs
- Rear panel USB 2.0 port
- Open GL ES 2.0—advanced 3D graphic acceleration

## BENEFITS

- Superior, all-digital video and sound quality for a true home theater experience
- Embedded IP networking supports high-bandwidth data applications
- 802.11ac 3x3 5GHz Wi-Fi
- Supports digital TV functionality, including the interactive program guide (IPG), video on demand (VoD), and commercial-free, CD-quality music
- Advanced hardware platform supports feature-rich applications and graphics
- Process IP video transport
- Rovi®, HDCP, DTCP, IPRM and CGMS-A content protection schemes on the respective interfaces

## GENERAL SPECIFICATIONS

INPUT FREQUENCY	
IP	1125 to 1525 MHz (1675 MHz MoCA 2.0)
Home Network	MoCA-compliant, 802.11ac Wi-Fi
DIGITAL INPUT LEVEL	
IP Data Carrier	MoCA
Frequency	1125 to 1525 MHz (1675 MHz MoCA 2.0)
Bandwidth	50 MHz/100 MHz (MoCA 2.0)
Level	0 dBm
OUTPUTS	
HDTV	HDMI
Standard TV	Composite Video (RCA)
Audio	Optical S/PDIF, Analog L/R
Data	USB 2.0, 10/100Base-T Ethernet, 802.11ac Wi-Fi (backwards compatible with 802.11b/g/n)
MEMORY	
DRAM	1GB
Flash	512MB
CPU Minimum	3000 MIPS
Video	MPEG-2 and MPEG-4
Video resolution	480i, 480p, 720p, 1080i, 1080p
Graphic resolution	Up to 1920 x 1080
Colors	32-bit
PHYSICAL	
Operating temperature	0 °C to 40 °C (32 °F to 104 °F)
Operating humidity	5 to 95% (noncondensing)
AC voltage	100 to 240 VAC, 50 Hz
Power dissipation	15 W nominal (depending on features)
Size	159.92 mm (D) x 48.42 mm (H) x 159.55 mm (W)
Weight	1.2 lbs. (including external power supply)

Specifications are subject to change without notice.



©ARRIS Enterprises, Inc. 2015 All rights reserved. No part of this publication may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from ARRIS Enterprises, Inc. ("ARRIS"). ARRIS reserves the right to revise this publication and to make changes in content from time to time without obligation on the part of ARRIS to provide notification of such revision or change. ARRIS and the ARRIS logo are all trademarks of ARRIS Enterprises, Inc. MoCA is a registered trademark of Multimedia over Coax Alliance. HDMI is a trademark of HDMI Licensing LLC. Dolby and the double-D symbol are registered trademarks of Dolby Laboratories. Wi-Fi®, the Wi-Fi CERTIFIED logo, and Wi-Fi Protected Access® (WPA), are registered trademarks of Wi-Fi Alliance. Wi-Fi CERTIFIED™ and Wi-Fi Protected Setup™ are trademarks of Wi-Fi Alliance. This product incorporates copy protection technology that is protected by U.S. patents and other intellectual property rights. Use of this copy protection technology must be authorized by Rovi Corporation, and is intended for home and other limited viewing uses only unless otherwise authorized by Rovi Corporation. Reverse engineering or disassembly is prohibited. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and the names of their products. ARRIS disclaims proprietary interest in the marks and names of others. All other product or service names are the property of their respective owners. The capabilities, system requirements and/or compatibility with third-party products described herein are subject to change without notice.