

FEATURES

- 60 dBmV ultra-high output at 1 GHz via GaN technology for Fiber Deep applications
- · 2x2 segmentable
- Four RF outputs, two auxiliary ports for power, and two fiber ports
- Multiple forward/return frequency split options
- Uses automotive blade style current shunts and JXP pads/equalizers
- Superior upstream performance via advanced universal digital return modules
- · Built-in, all-digital node status monitoring
- Redundant power supply option
- · Strand or pedestal mounting

The CommScope NC4000H3 series 2x2 segmentable node is designed to provide the utmost reliability, flexibility, and adaptability in an outdoor optical node platform and is ideal for Fiber Deep applications.

With an ultra-high output level of up to 60 dBmV (at 1002 MHz) available on all four RF output ports of the OA4324HG RF Output Amplifier, the NC4000H3 can be used to extend the reach of the coax distribution network in Fiber Deep architectures. Utilizing the standard or high gain optical receivers enables optical inputs between +3 and -10 dBm. This flexible and rugged platform is also scalable. Both downstream paths and upstream paths can be fully segmented using CommScope's universal digital return solutions. This includes a host of ITU CWDM and DWDM options further expanding the deployment of advanced "bandwidth-hungry" services into fiber-poor areas while reducing real estate and powering requirements in the field.



The NC4000H3 supports deployment of a wide range of field-hardened EDFAs and optical switches for extended fiber reach, routing options, and system reliability. Remote monitoring capability is provided with integrated network management eliminating the added cost of a third-party status monitoring transponder.

The NC4000H3 node platform also supports next-generation architectures and technologies such as Node PON, Node QAM, EPoC, and more, providing a seamless migration to support tomorrow's services.

SPECIFICATIONS

Characteristics		Specification	Specification		
Physical					
Dimensions		20" L x 9.5" W x 10.75" H (50.8 cm x 24.1 cm x 27.3 cm)			
Weight		38 lbs (17.1 kg)	38 lbs (17.1 kg)		
Housing Ports		6 AC/RF ports and 2 fiber ports			
Environmental					
Operating Temperature Range		-40° to +60°C (-40° to 140°F)			
Storage Temperature Range		-40° to +85°C (-40° to 185°F)			
Humidity		5% to 95% non-condensing			
General					
Passband Options		Reverse 5–45 MHz 5–60 MHz 5–65 MHz 5-85 MHz	Forward 54–1002 MHz 72–1002 MHz 85–1002 MHz 102-1002 MHz		
RF Test Points (Forward and Return)		-20 dB			
Flatness		± 1 dB	±1 dB		
Output Return Loss (at the Node Output)		> 16 dB			
Optical Input Range		-3 to +3 dBm into AR3x03G receiver -10 to +2 dBm into AR4x14G receiver			
Power Requirements					
Operating Input Voltage Range		44 to 95 V _{RMS} (50–60 Hz Quasi-Square \	44 to 95 V _{RMS} (50–60 Hz Quasi-Square Wave)		
Power Passing		15 A _{RMS}			
Power Supply Start-up Input Voltage		40–44 V _{RMS}			
Power Supply Turn Off Input Voltage		34–38 V _{RMS}			
Power Supply Efficiency		83% typical (PS4101) 73% typical (PS4001)			
DC Power Consumption		 73 W (standard configuration of 4 RF outputs and 1 optical Rx) 10 W (second Optical Receiver, AR4x14) 6 W (Return Transceiver, DT4250 with TR4000 SFP) 9 W (Node EDFA, single-width FA4500 series) 			
RF Performance for HFC App	plications ¹				
Channel Loading ²		High Level Fiber Deep Application			
	Up to 550 MHz	Analog NTSC			
	550–1002 MHz	256 QAM at -6 dBc			
Nominal Output Level (Per P	ort)				
	at 1002 MHz	60 dBmV			
	at 54 MHz	42 dBmV			
Nominal Slope					
	54/1002	18 dB linear			
Link Performance ³	CNIP	40 dP			
	CNR	49 dB			
	CSO	58 dB			
	СТВ	56.5 dB			

NOTES:

- Performance with 0.5 dBm input to node's Optical Receiver from a 1 GHz Model AT33xxG-A-2-AS Analog 1310 nm Transmitter
 For alternate channel loading performance, contact your CommScope Sales Representative
 Link performance, including transmitter (with CW channel loading to 550 MHz and 256QAM loading above 550 MHz at -6 dBc)

ORDERING INFORMATION

Model Name	Description
NC4000H3	A typical configuration of the NC4000H3 series optical node includes the NH4000-H housing with external test ports, one PS4101 power supply, one 51–1002 MHz optical receiver module (AR4214) with SC/APC connectors, the OA4324HG 4-port RF amplifier module, and JXP equalizers and pads. A backup PS4101 power supply may be separately ordered. Also available are optional plug-in modules that are described on separate data sheets; FA4500 series Optical Amplifiers, DT4250N Universal Digital Return Transceivers, optical or RF redundancy switches, and return ingress switch options. Please contact your CommScope sales representative for information regarding specific equipment configuration options to meet your requirements.

RELATED PRODUCTS

Digital Return Transmitter	Optical Patch Cords
SFPs	Optical Passives
Fiber Service Cable	Installation Services

Contact Customer Care for product information and sales:

United States: 866-36-ARRISInternational: +1-678-473-5656



 $\textbf{Note:} \ \mathsf{Specifications} \ \mathsf{are} \ \mathsf{subject} \ \mathsf{to} \ \mathsf{change} \ \mathsf{without} \ \mathsf{notice}.$

Copyright Statement: © 2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark $information see \\ \underline{https://www.commscope.com/trademarks}. All product names, trademarks and registered trademarks are property of their respective owners.$

1513808_RevG_NC4000H3