

# CBC781923T-DS-43 | E14F65P02



## Twin Quadplexer, 700/850/PCS/AWS-WCS, DC Sense, 4.3-10

- BTS-to-feeder and feeder-to-antenna application
- Automatic dc switching with dc sense
- Convertible mounting brackets
- New 4.3-10 connectors for improved PIM performance and size reduction
- Stackable in multiples with included hardware

## Product Classification

**Product Type** Quadplexer

## General Specifications

**Product Family** CBC781921W

**Color** Gray

**Common Port Label** Common

**Modularity** 2-Twin

**Mounting** Pole | Wall

**Mounting Pipe Hardware** Band clamps (2)

**RF Connector Interface** 4.3-10 Female

## Dimensions

**Height** 185 mm | 7.283 in

**Width** 273.5 mm | 10.768 in


**Depth** 114 mm | 4.488 in

**Ground Screw Diameter** 6 mm | 0.236 in

**Mounting Pipe Diameter Range** 40–160 mm

# CBC781923T-DS-43 | E14F65P02

## Outline Drawing



## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>License Band, Band Pass</b>	AWS 1700   CEL 850   LMR 750   PCS 1900   USA 700   USA 750   WCS 2300

## Electrical Specifications, dc Power/Alarm

<b>dc/AISG Pass-through Method</b>	Auto sensing
<b>dc/AISG Pass-through Path</b>	See logic table
<b>Lightning Surge Current</b>	5 kA
<b>Lightning Surge Current Waveform</b>	8/20 waveform
<b>Operating Current at Voltage</b>	15 mA @ 12 V   15 mA @ 24 V

# CBC781923T-DS-43 | E14F65P02

**Voltage** 7–30 Vdc

## Electrical Specifications, AISG

**AISG Carrier** 2176 KHz ± 100 ppm  
**Insertion Loss, maximum** 1 dB  
**Return Loss, minimum** 15 dB


## Electrical Specifications

Sub-module	1   2	1   2	1   2	1   2	1   2
<b>Branch</b>	1	2	3	4	4
<b>Port Designation</b>	698–803	824–894	1850–1990	AWS-WCS	AWS-WCS
<b>License Band</b>	LMR 750, Band Pass USA 700, Band Pass USA 750, Band Pass	CEL 850, Band Pass	PCS 1900, Band Pass	AWS 1700, Band Pass	WCS 2300, Band Pass

## Electrical Specifications, Band Pass

Frequency Range, MHz	698–803	824–894	1850–1990	1695–1780 2110–2200	2305–2360
<b>Insertion Loss, maximum, dB</b>	0.5	0.5	0.5	0.5	0.4
<b>Insertion Loss, typical, dB</b>	0.3	0.3	0.3	0.3	0.2
<b>Total Group Delay, maximum, ns</b>	50	55	55	25	25
<b>Return Loss, minimum, dB</b>	20	20	20	20	20
<b>Return Loss, typical, dB</b>	22	22	22	22	22
<b>Isolation, minimum, dB</b>	50	50	50	50	50
<b>Isolation, typical, dB</b>	65	55	55	55	55
<b>Input Power, RMS, maximum, W</b>	200	200	200	200	200
<b>Input Power, PEP, maximum, W</b>	2000	2000	2000	2000	2000
<b>3rd Order PIM, typical, dBc</b>	-161	-161	-161	-161	
<b>3rd Order PIM Test Method</b>	2 x 20 W CW tones	2 x 20 W CW tones	2 x 20 W CW tones	1 x 20 W AWS CW tone 1 x 20 W PCS CW tone	
<b>Higher Order PIM, typical, dBc</b>					-161
<b>Higher Order PIM Test Method</b>					2 x 20 W CW tones

## Block Diagram



### Logic Table

Combining Mode Operation (Ground Based)					DC/AISG Path Selection
RF Ports Input Voltage					
700 MHz	850 MHz	PCS	AWS/WCS	COMMON	700 MHz to COMMON "ON"
$7 \leq V \leq 30$	<7	<7	<7	<7	850 MHz to COMMON "ON"
<7	$7 \leq V \leq 30$	<7	<7	<7	PCS to COMMON "ON"
<7	<7	$7 \leq V \leq 30$	<7	<7	AWS/WCS to COMMON "ON"
<7	<7	<7	$7 \leq V \leq 30$	<7	Path selection will follow below priority: AWS (1), 700MHz (2), PCS (3), 850MHz (4)
Any 2 or more ports active $7 \leq V \leq 30$					<7

Splitting Mode Operation (Tower Top)					DC/AISG Path Selection
RF Ports Impedance DC (Load sensing)					
700 MHz	850 MHz	PCS	AWS/WCS	COMMON	COMMON to 700 MHz "ON"
open/load	short	short	short	$7 \leq V \leq 30$	COMMON to 850 MHz "ON"
short	open/load	short	short	$7 \leq V \leq 30$	COMMON to PCS "ON"
short	short	open/load	short	$7 \leq V \leq 30$	COMMON to AWS/WCS "ON"
short	short	short	open/load	$7 \leq V \leq 30$	DC/AISG will be routed to ALL ports with open/load impedance
Any 2 or more ports open/load impedance					$7 \leq V \leq 30$

### Environmental Specifications

**Operating Temperature** -40 °C to +65 °C (-40 °F to +149 °F)

**Corrosion Test Method** IEC 60068-2-11, 30 days

**Ingress Protection Test Method** IEC 60529:2001, IP67

### Packaging and Weights

**Included** Mounting hardware

**Mounting Hardware Weight** 0.5 kg | 1.102 lb

**Weight, without mounting hardware** 7.6 kg | 16.755 lb