

Fiber Optic Power Reducing Build Out Attenuator, singlemode LC/UPC, 12dB, blue

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

OBSOLETE


Product Classification

Regional Availability	Latin America North America
Product Type	Fiber attenuator
Product Series	FOA

General Specifications

Color	Blue
Interface	LC/UPC

Outline Drawing



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D
Attenuation, nominal	12 dB
Operating Wavelength	1430 – 1625 nm
Optical Components Standard	GR-910
Optical Power, maximum	250 mW
Return Loss, minimum	40 dB

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)