



## DLX to DLX Adapter

- Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

## Product Classification

|                               |   |
|-------------------------------|---|
| <b>Regional Availability</b>  | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>              | CommScope®  |
| <b>Product Type</b>           | Fiber adapter   |
| <b>Product Brand</b>          | DLX®  |
| <b>Product Series</b>         | FHD   |
| <b>Minimum Order Quantity</b> | 10  |

## General Specifications

|                              |                      |
|------------------------------|----------------------|
| <b>Body Style</b>            | Straight orientation |
| <b>Color</b>                 | Black                |
| <b>Interface</b>             | DLX                  |
| <b>Shuttered</b>             | No                   |
| <b>Total Ports, quantity</b> | 2                    |

## Optical Specifications

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| <b>Insertion Loss, maximum</b>      | 0.5 dB                               |
| <b>Insertion Loss, maximum note</b> | 0.5 dB mated included DLX connectors |
| <b>Return Loss, minimum</b>         | 65 dB                                |

## Environmental Specifications

|                                |                                      |
|--------------------------------|--------------------------------------|
| <b>Operating Temperature</b>   | -40 °C to +75 °C (-40 °F to +167 °F) |
| <b>Flammability Rating</b>     | UL 94 V-1                            |
| <b>Qualification Standards</b> | Telcordia GR-326-CORE                |
| <b>UV Resistance</b>           | UV stabilized                        |

## Packaging and Weights

**Packaging quantity** 10  
**Packaging Type** Bag

Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

