


# CBC426-DS-43 | E14F05P30



Diplexer, 380–960 MHz/1695–2690 MHz,dc Sense,4.3-10

- BTS-to-feeder and feeder-to-antenna application
- New 4.3-10 connectors for improved PIM performance and size reduction
- Automatic dc switching with dc sense
- Convertible mounting brackets

## Product Classification

**Product Type** Diplexer

## General Specifications


**Product Family** CBC426  
**Color** Gray  
**Common Port Label** ANT  
**Modularity** 1-Single  
**Mounting** Pole | Wall  
**Mounting Pipe Hardware** Band clamps (2)  
**RF Connector Interface** 4.3-10 Female  
**RF Connector Interface Body Style** Long neck

## Dimensions

**Height** 152 mm | 5.984 in  
**Width** 121 mm | 4.764 in  
**Depth** 56.5 mm | 2.224 in  
**Ground Screw Diameter** 6 mm | 0.236 in  
**Mounting Pipe Diameter Range** 40–160 mm

# CBC426-DS-43 | E14F05P30

## Outline Drawing



## Electrical Specifications

### Impedance

50 ohm

### License Band, Band Pass

APT 700 | AWS 1700 | CEL 850 | CEL 900 | DCS 1800 | EDD 800 | IMT 2100 | IMT 2600 | LMR 750 | LMR 800 | LMR 900 | PCS 1900 | TDD 1900 | TDD 2000 | TDD 2300 | TDD 2600 | USA 600 | USA 700 | USA 750 | WCS 2300

## Electrical Specifications, Common Port

### Composite Power, RMS

250 W

## Electrical Specifications, dc Power/Alarm

### dc/AISG Pass-through Method

Auto sensing

# CBC426-DS-43 | E14F05P30

<b>dc/AISG Pass-through Path</b>	See logic table
<b>Lightning Surge Current</b>	10 kA
<b>Lightning Surge Current Waveform</b>	8/20 waveform
<b>Voltage</b>	7–30 Vdc

## Electrical Specifications, AISG

<b>AISG Carrier</b>	2176 KHz ± 100 ppm
<b>Insertion Loss, maximum</b>	1 dB
<b>Return Loss, minimum</b>	15 dB


## Electrical Specifications

<b>Sub-module</b>	<b>1</b>	<b>1</b>
<b>Branch</b>	1	2
<b>Port Designation</b>	380-960	1695-2690
<b>License Band</b>	LMR 750, Band Pass LMR 800, Band Pass USA 700, Band Pass USA 750, Band Pass USA 600, Band Pass CEL 850, Band Pass	PCS 1900, Band Pass WCS 2300, Band Pass AWS 1700, Band Pass TDD 2600, Band Pass

## Electrical Specifications, Band Pass

<b>Frequency Range, MHz</b>	<b>380–960</b>	<b>1695–2690</b>
<b>Insertion Loss, typical, dB</b>	0.1	0.1
<b>Total Group Delay, typical, ns</b>	2	4
<b>Return Loss, typical, dB</b>	24	22
<b>Isolation, typical, dB</b>	65	63
<b>Input Power, RMS, maximum, W</b>	200	200
<b>Input Power, PEP, maximum, W</b>	2000	2000
<b>3rd Order PIM, minimum, dBc</b>	-161	-161
<b>3rd Order PIM Test Method</b>	2 x 20 W CW tones	2 x 20 W CW tones

## Block Diagram



## Logic Table

Combining Mode Operation (Ground Based)			
RF Ports Input DC Voltage			
380 to 960 MHz	1695 to 2690 MHz	COMMON	DC/AISG Path Selection
$7 \leq V \leq 30$	$< 7$	$< 7$	380 to 960 MHz to COMMON "ON"
$< 7$	$7 \leq V \leq 30$	$< 7$	1695 to 2690 MHz to COMMON "ON"
$7 \leq V \leq 30$	$7 \leq V \leq 30$	$< 7$	1695 to 2690 MHz to COMMON "ON"

Splitting Mode Operation (Tower Top)			
RF Ports Impedance DC (Load sensing)			
380 to 960 MHz	1695 to 2690 MHz	COMMON	DC/AISG Path Selection
open/load	short	$7 \leq V \leq 30$	COMMON to 380-960 "ON"
short	open/load	$7 \leq V \leq 30$	COMMON to 1695-2690 "ON"
open/load	open/load	$7 \leq V \leq 30$	ALL ports ON
short	short	$7 \leq V \leq 30$	ALL ports OFF

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	5%–100%
<b>Corrosion Test Method</b>	IEC 60068-2-11, 30 days
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Mounting Hardware Weight</b>	0.6 kg   1.323 lb
<b>Volume</b>	1 L
<b>Weight, without mounting hardware</b>	1.6 kg   3.527 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system